



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E22GDB2 II PSHPLL 2P Ma BKBZ R Eaton Corp

Catalog Number	E22GDB2
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM Non-Metallic Heavy-Duty Actuator Push-Pull Operator, Standard Actuator, Red, Plastic, Illuminated, No Light Unit, Two-Position, Maintained Push and Pull, E22 Series
Weight per unit	0.1000 (lbs/each)
Product Category	Push Button Components

### Features

actuator	Standard
dimensions	2.0000 IN X 2.0000 IN X 2.0000 IN

### Dimensions and Weight

Size	40 mm
------	-------

### Descriptions

Description	IL PSHPLL 2P MA BKBZ R
extra long description	ETN E22GDB2 IL PSHPLL 2P MA BKBZ R
Features	Eaton's 22.5 mm industrial heavy-duty pushbutton line offers a wide array of functional, smartly styled illuminated and non-illuminated pushbuttons, selector switches, push-pulls, action and twist-to-release operators. The complete line also includes transformer, full voltage, resistor, LED or neon light units.
Long Description	Eaton 22.5 mm Non-metallic Heavy-Duty Actuator Push-Pull Operator, Standard Actuator, Red, Plastic, Illuminated, No light unit, Two-position, Maintained push and pull, E22 Series
Product Type	II PSHPLL 2P Ma BKBZ R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113467511
Manufacturers Part Number	E22GDB2
UPC	782113467511

### Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	PUSHBUTTON

### Packaging

Carton	1
Weight Per each	0.1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard

UL 508, IEC 947-5-1 MTTA, CSA Certified, Lloyd's Register

Certified, CE Marked