



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E3PBSS 8X3.25X2.75 N4X 3H PB

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | E3PBSS |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Pushbutton Screw Cover Type 4X, 3PBX30.5MM, SS304 |
| Weight per unit | 2.8 (lbs/each) |
| Product Category | Control Station Enclosures |

Features

| | |
|-----------------|---------------------|
| ip rating | IP66 |
| Material | Stainless Steel 304 |
| Number of Holes | 3 |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Unpainted |
| Finish | Brushed #4 |

Dimensions and Weight

| | |
|--------|--------------|
| Depth | 2.75 |
| Height | 8 |
| Size | 3PB x 30.5mm |
| Width | 3.25 |

Descriptions

| | |
|------------------------|--|
| Description | 8X3.25X2.75 N4X 3H PB |
| extra long description | NVENT HOF E3PBSS 3 PB Enclosure 8.0 |
| Features | Punched specifically to house either 30.5-mm or 22.5-mm oil-tight pushbuttons, switches and pilot lights. Enclosures provide protection against dirt, dust, oil and water. See Mild Steel chapter for related mild steel enclosures. |
| Long Description | Pushbutton Screw Cover Type 4X, 3PBx30.5mm, SS304 |
| Product Type | 3 PB Enclosure 8.00X3.25X2.75 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510596309 |
| Manufacturers Part Number | E3PBSS |
| UPC | 783510596309 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL JUNCTION BOXES |
| Type | Stainless Steel Industrial Terminal and Junction Boxes |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 2.8 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Controls and Drives; Corrosive Environments; Hygienic Environments

nema rating

4X Watertight, corrosion-resistant