



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E48P4K1A Safety Interlock SWTCH - Plastic Din 1-N.C. 1-N.O.

Eaton Corp

Catalog Number	E48P4K1A
Manufacturer	Eaton Corp
Description	Safety Interlock Switch, E48, Cabinet Door Interlock, Screw Terminals, 10A At 240V, Din, Plastic, 1NC-1no
Weight per unit	0.3000 (lbs/each)
Product Category	Interlock Switches & Accy.

Features

connection	Screw Terminal
Contact Configuration	1 NC-1 NO
Contact Rating	10A at 240V
dimensions	5.0000 IN X 2.0000 IN X 2.0000 IN

Descriptions

Description	SAFETY INTERLOCK SWTCH - PLASTIC DIN 1-N.C. 1-N.O.
extra long description	ETN E48P4K1A Safety Interlock Switc
Features	The E48 Safety key interlock switch is designed for use with moveable guards, covers or doors which must be closed for operational safety. The switch is mounted to a rigid portion of the machine. The operation key (typically affixed to a moveable guard, cover or door) directly pulls NC contacts apart which interrupts the control circuit and stops machine operation. When the guard, cover or door is opened, the key is removed from the switch, thereby directly opening the NC contacts. The head mechanism is de
Long Description	Safety Interlock Switch, E48, Cabinet door interlock, Screw Terminals, 10A at 240V, DIN, Plastic, 1NC-1NO
Product Type	Safety Interlock Switch, 1NO/1NC Contacts

Manufacturer Information

Brand	Eaton
GTIN	00786685584508
Manufacturers Part Number	E48P4K1A
UPC	786685584508

Taxonomies, Classifications, and Categories

Category Description	Rotary Disconnects
Type	Safety key interlock switch

Packaging

Carton	1
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other Stationary Mach Equip In Factory - Other
Stationary Machinery and Equipment - In Factory

Operating Temperature
standard

-22
UL Listed