



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EC5T832GUNV3L Ecosystem Ballast 5 Input 3 Lamp 120-277V 32W

Lutron

Catalog Number	EC5T832GUNV3L
Manufacturer	Lutron
Description	Ecosystem 10 Percent 3-Wire and Ecosystem Digital Link Controlled T8 Linear and U-Bent 3 Lamps, Ballast Factor Of .85, With Leads, G-Can 32W/120/277V
Weight per unit	1.0 (lbs/each)
Product Category	Dimming Compact Fluorescent Ba

Features

amperage rating	0.72@120V/0.36@240V/0.31@277V
Ballast Factor	0.85
Lamp Type	T8 Linear and U-Bend
Minimum Starting Temperature	50
Number of Lamps	3
Power Factor	Greater than 0.95
start type	Programmed rapid
total harmonic distortion	Less than 10%
Voltage Rating	120/240/277
Wattage	32

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Height	1
Length	18
Width	2.38



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	ECOSYSTEM BALLAST 5 INPUT 3 LAMP 120-277V 32W
extra long description	LUT EC5T832GUNV3L ECOSYS BST 5 INPU
Long Description	EcoSystem 10 percent 3-Wire and EcoSystem Digital Link Controlled T8 Linear and U-Bent 3 lamps, ballast factor of .85, with leads, G-can 32W/120/277V
Product Type	Ecosys BST 5 Input T8 32W Gunv 3 Lamp
Special Features	Maximize the benefits of a lighting management system. Offers continuous, flicker-free 100 % to 10 % dimming; ideal for use where saving energy, increasing flexibility, and maximizing productivity are the goals of the lighting design. Integral sensor connection provides power for and responds to one occupancy sensor, one photo sensor, and one personal control input (infrared receiver or wallstation). Communicates status and sensor inputs over the EcoSystem digital link. Programmed rapid start design ensu

Manufacturer Information

Brand	Lutron
GTIN	00027557600811
Manufacturers Part Number	EC5T832GUNV3L
UPC	027557600811

Taxonomies, Classifications, and Categories

Category Description	DIMMING BALLASTS
Type	Ballast

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Lighting Control
Frequency Rating	50/60
Mounting	FIXTURE
standard	UL, CSA, S Mark certified, Class P thermal protected, ANSI, FCC