



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50KL204 E50 Operating Lever

Eaton Corp

Catalog Number	E50KL204
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Lever, Rotary Lever, Fork, 1.5 Inch Len, Die Cast Zinc, Nylatron Rollers 0.75 Inch Diameter 0.32 Inch Width, Both Rollers Inside Fork, 14-250F(-10-121C), Stainless Steel, Nylatron, Ul, Csa, Ce
Weight per unit	0.1500 (lbs/each)
Product Category	Limit Switch Arms, Actuators &

### Features

actuator	Fork lever
dimensions	2.8700 IN X 1.9200 IN X 0.6200 IN

### Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL204 E50 LS LEVER,FORK,NYL
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Lever,Rotary lever,fork,1.5 inch len,Die cast Zinc,Nylatron rollers 0.75 inch diameter 0.32 inch width,both rollers inside fork,14-250F(-10-121C),Stainless Steel,Nylatron,UL,CSA,CE
Product Type	E50 LS Lever, Fork, Nyl Roller .75IN, SM SD

### Manufacturer Information

Brand	Eaton
GTIN	00782113290935
Manufacturers Part Number	E50KL204
UPC	782113290935

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	CSA Certified,CE,UL Listed,RoHS Compliant,CE Marked