



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E51ALT1 Ind Prox Complete

Eaton Corp

Catalog Number	E51ALT1
Manufacturer	Eaton Corp
Description	Eaton E51 Nema Limit Switch Inductive Proximity Sensor, Inductive Proximity Sensor, E51 Modular, Top Sensing, Shielded, Output On (1 Led Per Output), Screw Terminals, 500 Ma Ac/DC Solid State Output, No or NC, 20-264 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Inductive Proximity Sensor

### Features

connection	Screw Terminal
dimensions	4.5300 IN X 1.5400 IN X 1.7800 IN

### Descriptions

Description	IND PROX COMPLETE
extra long description	ETN E51ALT1 IND PROX COMPLETE
Features	Eaton's E51 limit switch style modular sensors are available in thru-beam, reflex, polarized reflex, diffuse reflective and fiber optic sensing modes to solve a wide variety of sensing applications. Modular, plug-in components are easy to maintain, meaning less downtime and reduced inventory. Choose between 2-wire sensors with AC/DC operation and 4-wire sensors in either AC or DC styles. Connection options include terminal, mini-connector and various lengths of cable. Sensors can be ordered in component fo
Long Description	Eaton E51 NEMA limit switch inductive proximity sensor, Inductive Proximity Sensor, E51 Modular, Top Sensing, Shielded, Output ON (1 LED per output), Screw Terminals, 500 mA AC/DC solid state output, NO or NC, 20-264 Vac/dc
Product Type	Ind Prox Complete

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113312743
Manufacturers Part Number	E51ALT1
UPC	782113312743

### Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Limit switch inductive proximity sensor



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1.0499

## Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
environmental conditions	NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67
standard	UL Listed, CSA Certified