



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E51SAL Ind Prox Switch Body Only

Eaton Corp

Catalog Number	E51SAL
Manufacturer	Eaton Corp
Description	Eaton E51 Nema Limit Switch Inductive Proximity Sensor, Eaton Inductive Proximity Sensor, E51, Output On (1 Led Per Output), 500 Ma Ac/DC Solid State Output, 2-Wire Ac, No, 20-264 Vac/DC
Weight per unit	0.3000 (lbs/each)
Product Category	Sensor Accessories

Features

dimensions	2.0000 IN X 2.0000 IN X 5.2500 IN
Material	Die Cast Zinc

Dimensions and Weight

Depth	2
Height	5.25
Width	2

Descriptions

Description	IND PROX SWITCH BODY ONLY
extra long description	ETN E51SAL IND PROX SWITCH BODY ONL
Features	Eaton's E51 limit switch style modular sensors are available in thru-beam, reflex, polarized reflex, diffuse reflective and fiber optic sensing modes to solve a wide variety of sensing applications. Modular, plug-in components are easy to maintain, meaning less downtime and reduced inventory. Choose between 2-wire sensors with AC/DC operation and 4-wire sensors in either AC or DC styles. Connection options include terminal, mini-connector and various lengths of cable. Sensors can be ordered in component fo
Long Description	Eaton E51 NEMA limit switch inductive proximity sensor, Eaton Inductive Proximity Sensor, E51, Output ON (1 LED per output), 500 mA AC/DC solid state output, 2-wire AC, NO, 20-264 Vac/dc
Product Type	Ind Prox Switch Body Only

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113344935
Manufacturers Part Number	E51SAL
UPC	782113344935

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Limit switch inductive proximity sensor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
Operating Temperature standard	-13 UL Listed, CSA Certified