



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E55CAL12T111E 12MM STD Ind Prox Plastic 3W DC PNP

Eaton Corp

| | |
|------------------|---|
| Catalog Number | E55CAL12T111E |
| Manufacturer | Eaton Corp |
| Description | Tubular Inductive Proximity Sensor, E55, 4 MM Range, Straight, 12 MM, Unshielded, Output On, 3-Wire, 6.6 FT, 200 Ma, PVC, Nonmetallic, No PNP Open Collector, 10-30 VDC |
| Weight per unit | 0.5000 (lbs/each) |
| Product Category | Inductive Proximity Sensor |

Features

| | |
|------------|-----------------------------------|
| dimensions | 2.1700 IN X 0.4700 IN X 0.4700 IN |
|------------|-----------------------------------|

Descriptions

| | |
|------------------------|---|
| Description | 12MM STD IND PROX PLASTIC 3W DC PNP |
| extra long description | ETN E55CAL12T111E 12MM STD IND PROX |
| Features | 55 series photoelectric sensors are identical to the 50 series except without the interchangeable outputs or logic functions. They offer durability and high optical performance in a cost-effective, self-contained package. The 55 Series features sensors with AC and DC operation in a single unit. A relay option is available on these models that provides a 3 Amp SPDT relay output for high current switching. |
| Long Description | Tubular Inductive Proximity Sensor, E55, 4 mm range, Straight, 12 mm, Unshielded, Output ON, 3-wire, 6.6 ft, 200 mA, PVC, Nonmetallic, NO PNP open collector, 10-30 Vdc |
| Product Type | 12MM STD Ind Prox Plastic 3W DC PNP |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00782113888187 |
| Manufacturers Part Number | E55CAL12T111E |
| UPC | 782113888187 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | SENSORS |
| Type | Photoelectric Sensor |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.5 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Stationary Machinery and Equipment Outside Factory - Car Wash |
| environmental conditions | NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 13, IP66 |
| standard | CE,RoHS Compliant,CE Marked |