



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECS98V2CAHC1P7S3 Combo BRKR 150A 99A Nema 3R S611 480vac *Eaton Corp*

Catalog Number	ECS98V2CAHC1P7S3
Manufacturer	Eaton Corp
Description	Eaton S611 Soft Starter, Combination Reduced Voltage, Circuit Breaker, Standard Size CPT, 110V/50 HZ, 120V/60 HZ Secondary With Fuses, Nema 3R Enclosure, Start/Stop, Hand-Off-Auto Selector Switch, 150A Breaker, 99A, 460V
Weight per unit	200.0 (lbs/each)
Product Category	Soft Start Controllers & Start

Features

Coil Voltage	120V/60 Hz
media	Yes
Voltage Rating	460 V

Dimensions and Weight

Depth	35
Height	8.75
Size	99A max RVSS
Width	29.5

Descriptions

Description	COMBO BRKR 150A 99A NEMA 3R S611 480VAC
extra long description	ETN ECS98V2CAH-C1P7S3 Eaton S611 so
Features	The Eaton S611 is an innovative, economical soft starter combining advanced functionality, unsurpassed configuration flexibility, and an extremely comprehensive user interface. It is available in both open and enclosed control configurations to meet the needs of the commercial construction and OEM segment.
Long Description	Eaton S611 soft starter, Combination reduced voltage, circuit breaker, Standard size CPT, 110V/50 Hz, 120V/60 Hz secondary with fuses, NEMA 3R enclosure, START/STOP, HAND-OFF-AUTO selector switch, 150A breaker, 99A, 460V
Product Type	Eaton S611 Soft Starter
Special Features	Standard size control power transformer

Manufacturer Information

Brand	Eaton
GTIN	00786685620695
Manufacturers Part Number	ECS98V2CAH-C1P7S3
UPC	786685620695



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 200

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
..... Stationary Machinery and Equipment Outside Factory - Other

standard UL Listed,cUL Listed