



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EC0101 3/4" Weatherhead *Appleton/Oz Gedney*

Catalog Number	EC0101
Manufacturer	Appleton/Oz Gedney
Description	Features:3.64IN Depth X 2.8IN Height, (2) 3/8 In, (3) 13/32 In Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, Imc/Emt Service Masts, Standard:Ul 514B, Nema FB-1, Size:0.75IN, Material:Die Cast Zinc, Finish:Natural
Weight per unit	0.2900 (lbs/each)
Product Category	Service Entrance CBL Fittings

### Features

Material	Die Cast Zinc
----------	---------------

### Material, Color, and Finish

Finish	Unfinished
--------	------------

### Dimensions and Weight

Size	0.75
------	------

### Descriptions

Description	3/4" WEATHERHEAD
extra long description	EGS ECO-101 3/4 IN ALUM CLP ON ENTR
Long Description	Features:3.64IN Depth X 2.8IN Height, (2) 3/8 IN, (3) 13/32 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts, Standard:UL 514B, NEMA FB-1, Size:0.75IN, Material:Die Cast Zinc, Finish:Natural
Product Type	3/4 In Alum CLP On Entr Cap
Special Features	3.64 IN Depth X 2.8 IN Height, (2) 3/8 IN, (3) 13/32 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts

### Manufacturer Information

Brand	Appleton
GTIN	00687855251018
Manufacturers Part Number	ECO-101
UPC	687855251018

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Clamp-On Entrance Cap



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Package	50
Weight Per each	0.29

## Uses, Certifications, and Standards

Application	Clamp on Type For Use With Threaded or Unthreaded EMT or IMC Conduit
standard	UL 514B, NEMA FB-1