



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EC0106 2-1/2" Weatherhead *Appleton/Oz Gedney*

Catalog Number	EC0106
Manufacturer	Appleton/Oz Gedney
Description	Features:10.5IN Depth X 7IN Height, (3) 7/8 In, (1) 1 In, (3) 1 5/16 In Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, Imc/Emt Service Masts, Standard:Ul 514B, Nema FB-1, Size:2.5IN, Material:Aluminum, Finish:Natural
Weight per unit	3.9 (lbs/each)
Product Category	Service Entrance CBL Fittings

### Features

Material	Aluminum
----------	----------

### Material, Color, and Finish

Finish	Unfinished
--------	------------

### Dimensions and Weight

Size	2.5
------	-----

### Descriptions

Description	2-1/2" WEATHERHEAD
extra long description	EGS ECO-106 2-1/2 IN ALUM CLP ON EN
Long Description	Features:10.5IN Depth X 7IN Height, (3) 7/8 IN, (1) 1 IN, (3) 1 5/16 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts, Standard:UL 514B, NEMA FB-1, Size:2.5IN, Material:Aluminum, Finish:Natural
Product Type	2-1/2 In Alum CLP On Entr Cap
Special Features	10.5 IN Depth X 7 IN Height, (3) 7/8 IN, (1) 1 IN, (3) 1 5/16 IN Holes, Weather Resistant, For Threaded/Unthreaded Rigid Conduit, IMC/EMT Service Masts

### Manufacturer Information

Brand	Appleton
GTIN	00687855251063
Manufacturers Part Number	EC0106
UPC	687855251063

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Clamp-On Entrance Cap

### Packaging

Carton	1
Weight Per each	3.85



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Clamp on Type For Use With Threaded or Unthreaded EMT or  
IMC Conduit

standard

UL 514B, NEMA FB-1