



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EGE3060FFG E 3P 60A 25KA @ 415 & 480V Fixed Thermal Fixed Mag

Eaton Corp

|                  |  |
|------------------|--|
| Catalog Number   | EGE3060FFG   |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 60 A, 600Y/347 Vac, 35 Kaic At 240 Vac, 25 Kaic At 480 Vac, 18 Kaic At 600Y/347 Vac, Line and Load, 50/60 HZ |
| Weight per unit  | 2.9 (lbs/each)   |
| Product Category | 3 Pole   |

### Features

|                  |   |
|------------------|---|
| Current Rating   | 60 A  |
| dimensions       | 2.9900 IN X 3.0000 IN X 5.5000 IN                           |
| frame            | EG  |
| interrupt rating | 18 kAIC at 600Y/347 Vac35 kAIC at 240 Vac25 kAIC at 480 Vac |
| media            | Yes   |
| Poles            | 3   |
| Trip Type        | Fixed thermal, fixed magnetic                               |
| Voltage Rating   | 600Y/347 Vac  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | E 3P 60A 25KA @ 415 & 480V FIXED THERMAL FIXED MAG  |
| extra long description | ETN EGE3060FFG E 3P 60A 25kA 415&48   |
| Features               | The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren |
| Long Description       | Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 60 A, 600Y/347 Vac, 35 kAIC at 240 Vac, 25 kAIC at 480 Vac, 18 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz  |
| Product Type           | E 3P 60A 25KA 415&480V FXD Therm FXD Mag  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782114876770 |
| Manufacturers Part Number | EGE3060FFG     |
| UPC                       | 782114876770   |

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | MOLDED CASE BREAKERS        |
| Type                 | Molded case circuit breaker |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 2.93 |

## Uses, Certifications, and Standards

|                  |  |
|------------------|--|
| Application      | Elec Assemblies, Panels & OEM - Electrical Assemblies and<br>EOEMs - Other |
| Frequency Rating | 50/60 Hz   |
| standard         | UL Listed, CSA Certified, IEC Rated, CE Marked                             |