

# Eaton ECN5512CAE-C1R63/C

Catalog Number: ECN5512CAE-C1R63/C

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, Wired for 480V, NEMA 3R steel enclosure, NEMA size 1, 220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary, 4-20A solid-state relay without ground fault, 30A breaker



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Industrial pump panel	ECN5512CAE-C1R63/C
<b>UPC</b>	<b>Product Length/Depth</b>
786685547183	8.47 in
<b>Product Height</b>	<b>Product Width</b>
38.4 in	18.86 in
<b>Product Weight</b>	<b>Warranty</b>
75 lb	1 year

## Certifications

UL Listed  
cUL Listed  
OSHDP Certified

## defaultTaxonomyAttributeLabel

### Enclosure

NEMA 3R

### Enclosure material

Painted steel

### Type

Circuit breaker disconnect

### Circuit breaker rating

30A

### Overload relay

4-20A solid-state relay without ground fault

### Size

NEMA size 1

### Special features

Wired for 480V

### System voltage

220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary

## Resources

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECN5512CAE-C1R63/C](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton ECN5512CAE-C1R63/C

Catalog Number: ECN5512CAE-C1R63/C

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, Wired for 480V, NEMA 3R steel enclosure, NEMA size 1, 220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary, 4-20A solid-state relay without ground fault, 30A breaker



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Industrial pump panel	ECN5512CAE-C1R63/C
<b>UPC</b>	<b>Product Length/Depth</b>
786685547183	8.47 in
<b>Product Height</b>	<b>Product Width</b>
38.4 in	18.86 in
<b>Product Weight</b>	<b>Warranty</b>
75 lb	1 year

## Certifications

UL Listed  
cUL Listed  
OSHDP Certified

## defaultTaxonomyAttributeLabel

### Enclosure

NEMA 3R

### Enclosure material

Painted steel

### Type

Circuit breaker disconnect

### Circuit breaker rating

30A

### Overload relay

4-20A solid-state relay without ground fault

### Size

NEMA size 1

### Special features

Wired for 480V

### System voltage

220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary

## Resources

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECN5512CAE-C1R63/C](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)