



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ELL1G Ocal 1"X90 Gray PVC CTD Elbow STL

*Abb Installation Products, Inc*

Catalog Number	ELL1G
Manufacturer	Abb Installation Products, Inc
Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1 Inch/27 Metric, Angle 90 Degrees, Radius 5-3/4 Inch/146.05 Millimeters, Offset 8 Inch/203.20 Millimeters, Straight End 2-1/4 Inch/57.15 Millimeters, Unbent Length 13.53 Inch/343.71 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Weight per unit	2.2 (lbs/each)
Product Category	Steel

### Material, Color, and Finish

Color	Gray
Finish	Hot Dip Galvanized

### Dimensions and Weight

Depth	13.53
-------	-------

### Descriptions

Description	OCAL 1"X90 GRAY PVC CTD ELBOW STL
extra long description	ABB ELL1-G PVC CTD ELBOW 90D 1IN ST
Long Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1 Inch/27 Metric, Angle 90 Degrees, Radius 5-3/4 Inch/146.05 Millimeters, Offset 8 Inch/203.20 Millimeters, Straight End 2-1/4 Inch/57.15 Millimeters, Unbent Length 13.53 Inch/343.71 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Product Type	PVC CTD Elbow 90D 1IN Steel Gray
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size

### Manufacturer Information

Brand	OCAL
GTIN	00704508369880
Manufacturers Part Number	ELL1-G
UPC	704508369880

### Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
Type	Conduit Elbow - Standard Radius

### Trade Size

Trade Size	1 in , 27 mm
------------	--------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Weight Per each	2.23

## Uses, Certifications, and Standards

Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
standard	cULus E46453, CSA