



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ELL2G Ocal 2"X90 Gray PVC CTD Elbow STL

Abb Installation Products, Inc

Catalog Number	ELL2G
Manufacturer	Abb Installation Products, Inc
Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2 Inch/53 Metric, Angle 90 Degrees, Radius 9-1/2 Inch/241.30 Millimeters, Offset 13 Inch/330.20 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 21.92 Inch/556.83 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Weight per unit	6.9 (lbs/each)
Product Category	Steel

Material, Color, and Finish

Color	Gray
Finish	Hot Dip Galvanized

Dimensions and Weight

Depth	21.92
-------	-------

Descriptions

Description	OCAL 2"X90 GRAY PVC CTD ELBOW STL
extra long description	ABB ELL2-G PVC CTD ELBOW 90D 2IN ST
Long Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2 Inch/53 Metric, Angle 90 Degrees, Radius 9-1/2 Inch/241.30 Millimeters, Offset 13 Inch/330.20 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 21.92 Inch/556.83 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Product Type	PVC CTD Elbow 90D 2IN Steel Gray
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size

Manufacturer Information

Brand	OCAL
GTIN	00704508370190
Manufacturers Part Number	ELL2-G
UPC	704508370190

Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
Type	Conduit Elbow - Standard Radius

Trade Size

Trade Size	2 in , 53 mm
------------	--------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	6
Weight Per each	6.9

Uses, Certifications, and Standards

Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
standard	cULus E46453, CSA