



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EMN25D31GSKM15 3P PB Manual Starter

Crouse-Hinds

Catalog Number	EMN25D31GSKM15
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Emn Nema Manual Pushbutton Starter, With Starter, 7.5 HP/10 HP, Square D Starter, Copper-Free Aluminum, Nema Size 1, Three-Pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 Model
Weight per unit	14.2 (lbs/each)
Product Category	Controls

Features

motor power	7.5-10 HP
Phase	3 Ph
Poles	3
Voltage Rating	200-230 Vac/380-575 Vac

Dimensions and Weight

Depth	7.94
Height	10.44
Size	10.44 x 7.94 x 7.80
Width	7.6

Descriptions

Description	3P PB MANUAL STARTER
extra long description	CRS-H EMN25 D31 GSK M15 MAN STARTER
Features	Crouse-Hinds series EMN pushbutton style compact manual NEMA starters are used on drilling rigs or mud agitators and shakers where flammable or explosive gases are present. Also used for fans and blowers, pumps, compressors and conveyors.
Long Description	Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter, With starter, 7.5 HP/10 HP, Square D starter, Copper-free aluminum, NEMA size 1, Three-pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 model
Product Type	Man Starter NEMA7 PB 3P Size 1 SQ D GSK
Special Features	Gasket

Manufacturer Information

Brand	Eaton
GTIN	00662276571143
Manufacturers Part Number	EMN25 D31 GSK M15
UPC	662276571143

Taxonomies, Classifications, and Categories

Category Description	1PH MANUAL STARTERS
----------------------	---------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	14.1699

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
Enclosure	Cast Aluminum
environmental conditions	where flammable, explosive gases present
Mounting	WALL MOUNT
standard	CSA Certified ,UL Listed