



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EGE3100FFG E 3P 100A 25KA @ 415 & 480V Fixed Thermal Fixed Ma Eaton Corp

Catalog Number	EGE3100FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 100 A, 600Y/347 Vac, 35 Kaic At 240 Vac, 25 Kaic At 480 Vac, 18 Kaic At 600Y/347 Vac, Line and Load, 50/60 HZ
Weight per unit	2.9 (lbs/each)
Product Category	3 Pole

### Features

Current Rating	100 A
dimensions	2.9900 IN X 3.0000 IN X 5.5000 IN
frame	EG
interrupt rating	18 kAIC at 600Y/347 Vac25 kAIC at 480 Vac35 kAIC at 240 Vac
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600Y/347 Vac

### Descriptions

Description	E 3P 100A 25KA @ 415 & 480V FIXED THERMAL FIXED MA
extra long description	ETN EGE3100FFG E 3P 100A 25kA 415&4
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 100 A, 600Y/347 Vac, 35 kAIC at 240 Vac, 25 kAIC at 480 Vac, 18 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz
Product Type	E 3P 100A 25KA 415&480V FXD Therm & Mag



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Eaton
GTIN	00782114876824
Manufacturers Part Number	EGE3100FFG
UPC	782114876824

## Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

## Packaging

Carton	1
Weight Per each	2.91

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60 Hz
standard	IEC Rated, CSA Certified, UL Listed, CE Marked