



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EN2800 28" Enclosure W/Screw On Cover

Pass & Seymour/Legrand

Catalog Number	EN2800
Manufacturer	Pass & Seymour/Legrand
Description	<P>This 28"" Enclosure Is The Perfect Solution For A Basic Structured Wiring System. It Features Larger Top Openings That Make Pulling Wire Easier As Well As Additional Knockouts, More Side Lances, and Side Tabs For More Flexible Mounting. It Includes A SC
Weight per unit	16.8 (lbs/each)
Product Category	Enclosures & Cabinets

Features

Cable Entry	(2) rectangular knockouts for 1-gang electrical box
Enclosure Size	28.0
face plate	Screw-on Cover
frame	Cold Rolled Steel
Material	Steel
media	Yes

Material, Color, and Finish

Color	White
Finish	Powder Coat

Dimensions and Weight

Depth	3.7"
Height	28.1"
Thickness	0.1
Width	14.3"

Descriptions

Description	28" ENCLOSURE W/SCREW ON COVER
extra long description	OnQ EN2800 28 ENCL W/SCREW ON COVER
Long Description	<p>This 28"" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a sc
Product Type	28 Encl W/Screw On Cover
Special Features	Flanged covers hide drywall openings- Flush and surface-mounted- Mounting tabs provide correct flush-mount position



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428023111
Manufacturers Part Number	EN2800
UPC	804428023111

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	ENCLOSURE

Packaging

Carton	1
Weight Per each	16.82

Uses, Certifications, and Standards

Application	Residential
Mounting standard	Surface or Flush CSA, ROHS, CULUS, UL, UL (UL985, UL1023, UL1863), cULus, CSA, RoHS