



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ESGTS2 #14-2 Awg Gel Tap Splice Kit (W/Connector)

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | ESGTS2   |
| Manufacturer     | Nsi Industries   |
| Description      | Easy-Splice Gel Tap Splice Kit With Connector For #14 - #2 Awg<br>The Easy-Splice Gel Tap Splice Kit Provides A Fast and Simple Method For Connecting, Insulating, and Environmentally Sealing Low-Voltage Splices. The Splice Kit Is Designed For Underground and Overhead Environments and Is Useful For Street Lighting Applications. The Splice Kit'S Dual-Rated Mechanical Connector Splices A Wide Range Of Cables, Including Copper and Aluminum. The Connector'S Four Port Design Allows Maximum Inventory Flexibility. TH |
| Weight per unit  | 0.1600 (lbs/each)  |
| Product Category | Splicing & Terminating Kits  |

### Features

|                |           |
|----------------|-----------|
| Cable Size     | 14-2 AWG  |
| Cable Type     | Class A-B |
| Voltage Rating | 1000 V    |
| Warranty       | 1 YEAR    |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | #14-2 AWG GEL TAP SPLICE KIT (W/CONNECTOR)   |
| extra long description | NSI ESGTS-2 Easy-Splice Gel 2/0 SL   |
| Features               | Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG<br>The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th |
| Long Description       | Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG<br>The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th |
| Product Type           | Easy-Splice Gel 2/0 SL   |
| Special Features       | Four Port Design With Dual Rated Mecahnical Connector  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381168634 |
| Manufacturers Part Number | ESGTS-2        |
| UPC                       | 662381168634   |

## Taxonomies, Classifications, and Categories

|                      |                                    |
|----------------------|------------------------------------|
| Category Description | SPLICE KITS                        |
| Type                 | Gel Tap Splice Kits With Connector |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 3    |
| Weight Per each | 0.16 |

## Uses, Certifications, and Standards

|                                |   |
|--------------------------------|---|
| Application                    | Splicing Wire                               |
| Operating Temperature standard | -40 C To 90 C<br>ANSI C119.1-1986 Qualified |