



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESGTS2 #14-2 Awg Gel Tap Splice Kit (W/Connector)

Nsi Industries

| | |
|------------------|--|
| Catalog Number | ESGTS2 |
| Manufacturer | Nsi Industries |
| Description | Easy-Splice Gel Tap Splice Kit With Connector For #14 - #2 Awg The Easy-Splice Gel Tap Splice Kit Provides A Fast and Simple Method For Connecting, Insulating, and Environmentally Sealing Low-Voltage Splices. The Splice Kit Is Designed For Underground and Overhead Environments and Is Useful For Street Lighting Applications. The Splice Kit'S Dual-Rated Mechanical Connector Splices A Wide Range Of Cables, Including Copper and Aluminum. The Connector'S Four Port Design Allows Maximum Inventory Flexibility. TH |
| Weight per unit | 0.1600 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------|-----------|
| Cable Size | 14-2 AWG |
| Cable Type | Class A-B |
| Voltage Rating | 1000 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | #14-2 AWG GEL TAP SPLICE KIT (W/CONNECTOR) |
| extra long description | NSI ESGTS-2 Easy-Splice Gel 2/0 SL |
| Features | Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th |
| Long Description | Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th |
| Product Type | Easy-Splice Gel 2/0 SL |
| Special Features | Four Port Design With Dual Rated Mecahnical Connector |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381168634 |
| Manufacturers Part Number | ESGTS-2 |
| UPC | 662381168634 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | SPLICE KITS |
| Type | Gel Tap Splice Kits With Connector |

Packaging

| | |
|-----------------|------|
| Carton | 3 |
| Weight Per each | 0.16 |

Uses, Certifications, and Standards

| | |
|--------------------------------|---|
| Application | Splicing Wire |
| Operating Temperature standard | -40 C To 90 C ANSI C119.1-1986 Qualified |