ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



ET05 DIGITAL POCKET THERMOMETER

KLEIN TOOLS

Catalog Number	ET05
Manufacturer	KLEIN TOOLS
Description	Klein Tools ET05 is a digital thermometer that takes ambient and direct-contact readings in both Fahrenheit (°F) and Celsius (°C) scales. The rugged, portable design makes it the choice of HVAC field service teams. The protective sheath cleverly serves as a handle to extend reach.
Weight per unit	0.0870 (lbs/each)
Product Category	Meters, Panel Instruments

Features

Accuracy	Room Temperature Accuracy of +/- 2.7°F (+/- 1.5°C)
Material	Stainless Steel Probe
Overall Height	0.94" (2.4 cm)
Overall Width	1.08" (2.7 cm)
Range	-40°F to 482°F (-40°C to 250°C)
Response Time	3 Seconds
Display	Digital
Included	Pocket Thermometer; Batteries
Media	Yes

Dimensions and Weight

Overall Length	6.5" (16.5 cm)

Descriptions

Description	DIGITAL POCKET THERMOMETER
Features	Klein Tools ET05 is a digital thermometer that takes ambient and direct-contact readings in both Fahrenheit (°F) and Celsius (°C) scales. The rugged, portable design makes it the choice of HVAC field service teams. The protective sheath cleverly serves as a handle to extend reach.
Long Description	Klein Tools ET05 is a digital thermometer that takes ambient and direct-contact readings in both Fahrenheit (°F) and Celsius (°C) scales. The rugged, portable design makes it the choice of HVAC field service teams. The protective sheath cleverly serves as a handle to extend reach.
Product Type	Digital Pocket Thermometer
Special Features	Max/Min, Hold and Average Functions; Auto Power Off
Extra Long Description	KLE ET05 Digital Pocket Thermometer

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Klein Tools
GTIN	00092644690600
Manufacturers Part Number	ET05
UPC	783523

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Digital Thermometer

Packaging

Carton	1
Package	4
Weight	1.40 oz (39.0 g)
Weight Per Each	0.0870 (lbs/each)

Uses, Certifications, and Standards

Application	Ambient and Direct-Contact Temperature Readings

DIGITAL POCKET THERMOMETER

ET05



°F °C


-40° – 482° F
-40° – 250° C

3 m

CE

KLEIN TOOLS®

For Professionals… Since 1857™



DIGITAL POCKET THERMOMETER

ET05

HVAC\R

Rugged, portable design makes the **ET05** the perfect choice for HVAC professionals.

- User selectable Fahrenheit and Celsius temperature measurements
- Range -40 to 482° F (-40 to 250° C) with 0.1 degree resolution
- Lightweight, compact tool with pocket clip provides easy storage and quick access
- Auto-power off after 15 minutes conserves battery life

HOLD | MAX/MIN | AVG | APO

3 m

Power On/Off Button

°F/°C Select Button
toggles between Fahrenheit (°F) and Celsius (°C)

Backlit LCD Display
for easy viewing in low light

HOLD/MAX/MIN/AVG Button
to capture maximum, minimum and average values

Protective Sheath/Handle
open sheath provides stable ambient air measurement; can be used as a handle for extended reach





Pocket Clip
also doubles as battery compartment for the device



3" Stainless Steel Probe
FDA GRAS-compliant

Thermometer is NOT intended for use on people or animals.

Cat. No.	UPC# 0-92644+	Batteries	Height	Width	Depth	Weight (oz.)
ET05	69060-0	2x LR44	6.5" (165 mm)	1.08" (27 mm)	0.96" (24 mm)	1.3 (37 g)

KLEIN TOOLS® EST. 1857
For Professionals... Since 1857™

See our complete line of **Test & Measure and HVAC** products
www.kleintools.com

Patent Pending

160 YEARS 1857—2017

© 2017 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
96505 Rev. 06/17 B