



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EVLEDC201 Haz Loc Led Ceiling Mount Fixt

Crouse-Hinds

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | EVLEDC201 |
| Manufacturer | Crouse-Hinds |
| Description | Eaton Crouse-Hinds Series Ev Led Light Fixture, 0.06 - 0.17A, Cool White, Ac Drive, Heat and Impact Resistant Glass Globe, With Guard, 1500 Lumens, 100 LM/W, Copper-Free Alum, No Mounting Module, >0.90 Power Factor, 100-277 Vac, 15W |
| Weight per unit | 14.8 (lbs/each) |
| Product Category | Led Hazardous Location Lightin |

Features

| | |
|-----------------|------------------------------------|
| amperage rating | 0.30;0.36;2.8 |
| average life | 50,000 |
| dimensions | 7.2500 IN X 7.2500 IN X 12.7500 IN |
| Voltage Rating | 10-30 VDC;120-277V |
| Wattage | 26;30;36 |

Descriptions

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | HAZ LOC LED CEILING MOUNT FIXT |
| extra long description | CRS-H EVLEDC201 LED LUMINAIRE EX LU |
| Features | The EV LED from Eaton's Crouse-Hinds Division is a Class I, Division 1 factory sealed LED light fixture for general illumination. The EV LED is built to perform effectively and economically in areas that may be difficult to service, expensive to shut down or any location requiring an increased degree of safety. Compared with conventional lighting, the EV LED consumes up to 85% less energy and typically lasts as long as 50,000 hours or more. The EV LED is available in two lumen output models, offering a |
| Long Description | Eaton Crouse-Hinds series EV LED light fixture, 0.06 - 0.17A, Cool white, AC drive, Heat and impact resistant glass globe, With guard, 1500 lumens, 100 lm/W, Copper-free alum, No mounting module, >0.90 power factor, 100-277 Vac, 15W |
| Product Type | Led Luminaire Ex Luminaire Only 30W Cool |
| Special Features | Energy-efficient-up to 85% reduction in energy used, easy installation, no warm up required, Dark sky compliant, contains no hazrdous substances |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00662276273276 |
| Manufacturers Part Number | EVLEDC201 |
| UPC | 662276273276 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------------------|
| Category Description | LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING |
| Type | Light fixture |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 14.8 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------------------------------------------------------------|
| Application | Ind Facilities & Factories - Facility: Lighting and Lighting Controls |
| Mounting | bulkhead mount;ceiling mount;pendant mount;stanchion mount;wall mount |