



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EWZ120 Astro 277 Clock *Nsi Industries*

Catalog Number	EWZ120
Manufacturer	Nsi Industries
Description	The Tork EWZ120 7-Day Astronomic Digital Timer Is Designed For 30 Amp / 120-277 Volt Loads and Has A Noryl Plastic Enclosure With A Locking Hasp For Outdoor Use. Automate Your Home or Office to Save Energy and Money Using The Intuitive Programming Interface to Activate Lights or Signage. Features One SPDT Output Channel With Automatic Voltage Detection. Designed For Commercial Applications Including Outdoor Lighting, Motors, Security or Parking Lot Lights, and Heating or Air Conditioning Equipment.
Weight per unit	2.0 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Screw
Contact Rating	120-277 VAC
Phase	Single Phase
Poles	1
Timing Range	7 DAY

Dimensions and Weight

Size	L=5.062 - H=8.312 - W=3.062
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	ASTRO 277 CLOCK
extra long description	TORK EWZ120 Astro Digital Timer SPD
Features	Digital timers simplify your life by automating repeating parts of your schedule, saving the user time, energy and money. The EWZ120 is a 7-day astronomic lighting control timer, ideal for applications in the home, office, factory, church or school. Use a photocell sensor to detect when the ambient light level drops below a programmable threshold, then turn on everything from signage to meeting room lights. Program in up to 20 different on/off settings with unique schedules for each day of the week using t
Long Description	The TORK EWZ120 7-Day Astronomic Digital Timer is designed for 30 amp / 120-277 volt loads and has a Noryl plastic enclosure with a locking hasp for outdoor use. Automate your home or office to save energy and money using the intuitive programming interface to activate lights or signage. Features one SPDT output channel with automatic voltage detection. Designed for commercial applications including outdoor lighting, motors, security or parking lot lights, and heating or air conditioning equipment.
Product Type	Astro Digital Timer SPDT
Special Features	20 On-Off Set Points - Daylight Savings Auto - Leap Year Automatic Compensation

Manufacturer Information

Brand	NSi
GTIN	00786261824714
Manufacturers Part Number	EWZ120
UPC	786261824714

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	7 Day Astronomic Time Switch - 1 Or 2 Channel

Packaging

Carton	1
Weight Per each	2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 3R Plastic Indoor-Outdoor With Locking Hasp
environmental conditions	-40 to + 149 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to + 149 F
standard	cULus