



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ESGTS2 #14-2 Awg Gel Tap Splice Kit (W/Connector)

*Nsi Industries*

Catalog Number	ESGTS2
Manufacturer	Nsi Industries
Description	Easy-Splice Gel Tap Splice Kit With Connector For #14 - #2 Awg The Easy-Splice Gel Tap Splice Kit Provides A Fast and Simple Method For Connecting, Insulating, and Environmentally Sealing Low-Voltage Splices. The Splice Kit Is Designed For Underground and Overhead Environments and Is Useful For Street Lighting Applications. The Splice Kit'S Dual-Rated Mechanical Connector Splices A Wide Range Of Cables, Including Copper and Aluminum. The Connector'S Four Port Design Allows Maximum Inventory Flexibility. TH
Weight per unit	0.1600 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Cable Size	14-2 AWG
Cable Type	Class A-B
Voltage Rating	1000 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Black
-------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	#14-2 AWG GEL TAP SPLICE KIT (W/CONNECTOR)
extra long description	NSI ESGTS-2 Easy-Splice Gel 2/0 SL
Features	Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th
Long Description	Easy-Splice Gel Tap Splice Kit with Connector for #14 - #2 AWG The Easy-Splice gel tap splice kit provides a fast and simple method for connecting, insulating, and environmentally sealing low-voltage splices. The splice kit is designed for underground and overhead environments and is useful for street lighting applications. The splice kit's dual-rated mechanical connector splices a wide range of cables, including copper and aluminum. The connector's four port design allows maximum inventory flexibility. Th
Product Type	Easy-Splice Gel 2/0 SL
Special Features	Four Port Design With Dual Rated Mecahnical Connector

## Manufacturer Information

Brand	NSi
GTIN	00662381168634
Manufacturers Part Number	ESGTS-2
UPC	662381168634

## Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Gel Tap Splice Kits With Connector

## Packaging

Carton	3
Weight Per each	0.16

## Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature standard	-40 C To 90 C ANSI C119.1-1986 Qualified