



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESX1LEDP450KR3MV ESX1 Led P4 50K R3 Mvolt Upa BLS DDBXD M2 *Lithonia Lighting - Acuity*

Catalog Number	ESX1LEDP450KR3MV
Manufacturer	Lithonia Lighting - Acuity
Description	The Lithonia Lighting Esx Led Area Luminaire Provides The Combination Of Best Product Value, Best Price and Best Delivery. Esx Is Ideal For One-For-One Replacement Of Hid Area Lighting and Provides Up to 76% Energy Savings, Long Service Life and Fast Payback. All Esx Luminaires Feature Adjustable Light Output, Providing Two Light Levels From One Product, Allowing Greater Flexibility While Helping Reduce Inventory Costs. The Luminaires Also Feature A Reversible Arm That Allows For Mounting On Both Round and
Weight per unit	11.7 (lbs/each)
Product Category	Lighting

Features

average life	60,000
dimensions	19.94 x 12 x 2.87
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	21,000 LM,22,000 LM,23,000 LM,24,000 LM,25,000 LM
Material	Aluminum
Maximum Operating Temperature	40
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Wattage	200

Material, Color, and Finish

Color	Bronze
color rendering index (cri)	70
color temperature	5000
Finish	Gloss
fixture material	aluminum
Lens Color	Clear
Lens Material	Glass
Style	CONTEMPORARY



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	2.87
Length	19.94
Size	19.94x12x2.87 IN
Width	12

Descriptions

Description	ESX1 LED P4 50K R3 MVOLT UPA BLS DDBXD M2
extra long description	LITH ESX1 LED P4 50K R3 MVOLT UPA B
Features	Contractor Select
Long Description	The Lithonia Lighting ESX LED area luminaire provides the combination of best product value, best price and best delivery. ESX is ideal for one-for-one replacement of HID area lighting and provides up to 76% energy savings, long service life and fast payback. All ESX luminaires feature adjustable light output, providing two light levels from one product, allowing greater flexibility while helping reduce inventory costs. The luminaires also feature a reversible arm that allows for mounting on both round and
Product Type	Area Light

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994838531
Manufacturers Part Number	ESX1 LED P4 50K R3 MVOLT UPA B
UPC	194994838531

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	AREA LIGHT

Packaging

Carton	1
Weight	11.24
Weight Per each	11.73

Uses, Certifications, and Standards

Application	Automotive & Parking, Offices & Banks, Retail
environmental conditions	OUTDOOR
Mounting	Arm Mount, Surface
standard	C-UL-USDLC Premium, Nighttime Friendly