



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ET218 3/4" to 1/2" Entr Tee *Crouse-Hinds*

Catalog Number	ET218
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Et Tee, Rigid/Imc, Feraloy Iron Alloy, 3/4"-1/2"-1/2"
Weight per unit	1.0 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	4.0000 IN X 1.2500 IN X 2.6300 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Descriptions

Description	3/4" TO 1/2" ENTR TEE
extra long description	CRS-H ET218 3/4-1/2-1/2 IRON DIV 1
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series Condulet ET tee, Rigid/IMC, Feraloy iron alloy, 3/4"-1/2"-1/2"
Product Type	3/4-1/2-1/2 Iron Div 1 Tee
Special Features	4 In Width X 1-1/4 In Depth X 2-5/8 In Height

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274318608
Manufacturers Part Number	ET218
UPC	782274318608

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	TEE

Packaging

Carton	1
Weight Per each	1.03



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 2 Group E F G, Class III
standard	UL 886, CSA C22.2