



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ET600 Insulation Resistance Tester

*Klein Tools*

Catalog Number	ET600
Manufacturer	Klein Tools
Description	The ET600 Is A Multi-Function Megohmmeter Capable Of Producing 125V, 250V, 500V, and 1000V Test Voltages For Insulation Resistance Measurements Up to 4000M . Also Tests Ac/DC Voltages Up to 1000V With Automatic Ranging True RMS Technology. Convenient Lock Function and Built-In Stand For Hands Free Operation. Dual-Function Backlit Display Monitors Process.
Weight per unit	1.1 (lbs/each)
Product Category	Test Equipment - Multimeters

### Features

Capacitance display functions included	— 4000 Count LCD Insulation Resistance, Voltage AC/DC, Resistance, and Continuity Tester; CAT III/CAT IV Safety Rated Test Leads; Heavy-duty Alligator Clip Test Leads; Batteries; Carrying Case; Instruction Manual
Material media	ABS, Polycarbonate, Electrical Components Yes
Overall Height	2.32" (5.9 cm)
Overall Width	3.59" (9.1 cm)
package quantity	1
Resistance	400 ohms Maximum
Temperature Range	—
Voltage	125V, 250V, 500V, and 1000V DC; 1000V AC/DC

### Material, Color, and Finish

Color	Orange/Black
-------	--------------

### Dimensions and Weight

Overall Length	7.93" (20.2 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	INSULATION RESISTANCE TESTER
extra long description	KLEIN ET600 Insulation Resistance T
Features	The ET600 is a multi-function Megohmmeter capable of producing 125V, 250V, 500V, and 1000V test voltages for insulation resistance measurements up to 4000M . Also tests AC/DC voltages up to 1000V with automatic ranging True RMS technology. Convenient lock function and built-in stand for hands free operation. Dual-function backlit display monitors process.
Long Description	The ET600 is a multi-function Megohmmeter capable of producing 125V, 250V, 500V, and 1000V test voltages for insulation resistance measurements up to 4000M . Also tests AC/DC voltages up to 1000V with automatic ranging True RMS technology. Convenient lock function and built-in stand for hands free operation. Dual-function backlit display monitors process.
Product Type	Insulation Resistance Tester
Special Features	Lock Button for Insulation Resistance Testing

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644692420
Manufacturers Part Number	ET600
UPC	092644692420

## Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Insulation Resistance Tester

## Packaging

Carton	1
Weight	1.4 lb (0.6 kg)
Weight Per each	1.062

## Uses, Certifications, and Standards

Application	Installation, Troubleshooting, and Preventive Maintenance of Electrical Wiring and Electrical Equipment, Measures 1000V AC/DC, Resistance, and Continuity
standard	CAT IV 600V/CAT III 1000V, EN61557-1, EN61557-2, EN61557-4