



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EZB2060R Ez Box 20"W X 60"H, Unpainted Galvanized

*Eaton Corp*

Catalog Number	EZB2060R
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240V, BR, #14-4 Awg Cu/Al, Q1, Type BR Loadcenters
Weight per unit	54.0 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

### Features

dimensions	2.5000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	1
Voltage Rating	120/240 V

### Descriptions

Description	EZ BOX 20"W X 60"H, UNPAINTED GALVANIZED
extra long description	ETN BR120 Type BR Breaker 20A/1 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, single-pole, 120/240V, BR, #14-4 AWG Cu/Al, Q1, Type BR loadcenters
Product Type	Type BR Breaker 20A/1 Pole 120/240V 10K

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786676362108
Manufacturers Part Number	BR120
UPC	786676362108

### Taxonomies, Classifications, and Categories

Category Description	Panelboard Boxes, Covers, Latches, Directories
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	54



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy  
Generation - Conventional Energy - Conventional Energy  
Other Marine Vessels and Equipment - Marine Vessels and Equipment -  
Other Datacenters - IT Space: CI and Hyper Converged

standard

UL 489, Federal Specifications Classification W-C375