



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EZB2060R Ez Box 20"W X 60"H, Unpainted Galvanized

Eaton Corp

Catalog Number	EZB2060R
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240V, BR, #14-4 Awg Cu/Al, Q1, Type BR Loadcenters
Weight per unit	54.0 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

dimensions	2.5000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	EZ BOX 20"W X 60"H, UNPAINTED GALVANIZED
extra long description	ETN BR120 Type BR Breaker 20A/1 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, single-pole, 120/240V, BR, #14-4 AWG Cu/Al, Q1, Type BR loadcenters
Product Type	Type BR Breaker 20A/1 Pole 120/240V 10K

Manufacturer Information

Brand	Eaton Corp
GTIN	00786676362108
Manufacturers Part Number	BR120
UPC	786676362108

Taxonomies, Classifications, and Categories

Category Description	Panelboard Boxes, Covers, Latches, Directories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	54



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy
Generation - Conventional Energy - Conventional Energy
Other Marine Vessels and Equipment - Marine Vessels and Equipment -
Other Datacenters - IT Space: CI and Hyper Converged

standard

UL 489, Federal Specifications Classification W-C375