



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EZ25D0 Ez 25 Cu-In. 2G Old Work

Cantex, Inc

Catalog Number	EZ25D0
Manufacturer	Cantex, Inc
Description	2-Gang 25 Cu. In. Ez Box Old Work Residential Electrical Switch and Outlet Box With Ez Mount Clamps and Wire Clamps Gray
Weight per unit	0.3130 (lbs/each)
Product Category	Non-Metallic

Features

Cable Entry	6 integral wire clamps
installation type	Old Work
Material	PVC
Mounting Type	flange & swing tab
Number of Gangs	2-gang

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	2-Gang
------	--------

Descriptions

Also Known As...	Remodeling box Pop-in Box Old Work Box old-work box Cut in box Retrofit Junction Box
Construction	old work
Description	EZ 25 CU-IN. 2G OLD WORK
extra long description	CTX EZ25DO 25 CU IN 2 GANG OLD WORK
Features	CANTEX EZ25DO EZ BOX is a 2-Gang 25 cu. in. renovation (old work) electrical switch or outlet box is for residential or light commercial renovation (old work) projects when a 2-gang box is needed. EZ mount flanges, winged swing tabs and built in wire clamps make installation easy and cost effective.
Long Description	2-Gang 25 cu. in. EZ BOX Old Work Residential Electrical Switch and Outlet Box with EZ Mount Clamps and Wire Clamps Gray
Product Type	25 Cu In 2 Gang Old Work Box
Special Features	wing tab



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PVC & Accessories
GTIN	00088700019911
Manufacturers Part Number	EZ25DO
UPC	088700019911

Taxonomies, Classifications, and Categories

Category Description	PLASTIC BOXES
Type	2-gang old work switch & outlet box

Packaging

Carton	1
Package	30
Weight Per each	0.313

Uses, Certifications, and Standards

Application	2-gang old work switch & outlet box
Mounting standard	flange & swing tab UL 2 hr. fire-rated