

# GE Lighting

## System Limited Warranty

(See the GE Lighting System and Ballast Limited Warranty at [www.gelighting.com/warranty](http://www.gelighting.com/warranty) for full details and specific lamp cycle requirements.)

### GE Lamps Operating on GE Ballasts

	Lamp Warranty <sup>2</sup>		Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty <sup>5</sup>	
Compact Fluorescent Lamp <sup>4</sup>	When Operated on GE Programmed Rapid-Start Ballasts	When Operated on GE Instant-Start Ballasts			
Double Biax <sup>®</sup> : 13-, 18-, 26-watt "DBX" (4-pin base types only)	2 years	-	5 years	-	
Triple Biax <sup>®</sup> : 13-, 18-, 26-, 32-, 42-watt "TBX"	2 years	-	5 years	-	
High-Output Biax <sup>®</sup> : 57-watt and 70-watt "QBX"	2 years	-	5 years	-	
High Lumen Biax <sup>®</sup> 27 W and 39 W	1 year	-	5 years	-	
High Lumen Biax <sup>®</sup> 55 W <sup>6</sup>	2 years	-	5 years	-	
High Lumen Biax <sup>®</sup> Watt-Miser <sup>®</sup> 25 W (F40/25BX)	3 years	2.5 years	5 years	-	
High Lumen Biax <sup>®</sup> 40 W (F40/30BX)	2 years	1 year	5 years	-	
Linear Fluorescent Lamp <sup>1,4</sup>	When Operated on GE Programmed Rapid-Start Ballasts	When Operated on GE Instant-Start Ballasts	Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty <sup>5</sup>	
F17T8/XL, F25T8/XL, F32T8 (SP, SPP & SPX)	3 years	2.5 years	5 years	2 years	
F17T8/XL/WM, F25T8/XL/WM	3 years	3 years	5 years	2 years	
F28T8/XL/SPP, F32T8/25W/SPP, F32T8/XL (SP & SPX)	4 years	3 years	5 years	2 years	
F32T8/XL/HL	4 years	4 years	5 years	2 years	
F28T8/XL/SPX, F32T8/SXL, F32T8/25W/SPX	5 years	4 years	5 years	2 years	
F28T8/SXL, F32T8/25W/SXL	7 years	5 years	5 years	2 years	
F96T8, F96T8/HO	-	2 years	5 years	-	
F96T8/XL (SP, SPP & SPX), F96T8/XL/WM, F96T8/XL/WMP, F96T8/54W/SPP, F96T8/49W (SPP & SPX)	-	3 years	5 years	-	
F28W/TS/HL	3 years	-	5 years	-	
F14T5/WM, F21T5/WM, F28T5/WM, F35T5/WM	3.5 years	-	5 years	-	
F14T5HE, F21T5HE, F28T5HE, F35T5HE, F54T5/47W, F24T5HO, F39T5HO, F54T5HO, F80T5HO, F54T5/WM	4 years	-	5 years	-	
F54T5/XL	5 years	-	5 years	-	
HID High Watt Lamps <sup>4</sup>	When Operated on GE Ballasts		Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty <sup>5</sup>	
CMH <sup>®</sup> ConstantColor <sup>®</sup> SPXX: 250-, 320-, 350-, 400-watt	1 year	-	5 years	2 years	
PulseArc <sup>®</sup> : 250-, 320-, 350-, 400-watt	1 year	-	5 years	2 years	
HID Low Watt Lamps <sup>4</sup>	Wattage/Type	When Operated on GE Ballasts		Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty
CMH <sup>®</sup> PAR	PAR20, PAR30L, PAR38, PAR64	6 months	-	5 years	-
CMH <sup>®</sup> MR16	All	6 months	-	5 years	-
CMH <sup>®</sup> GU6.5	All	6 months	-	5 years	-
CMH <sup>®</sup> G8.5	20 W	6 months	-	5 years	-
	39 W, 70 W	1 year	-	5 years	-
CMH <sup>®</sup> G12	20 W, 150 W	6 months	-	5 years	-
	39 W, 70 W	1 year	-	5 years	-
CMH <sup>®</sup> Double-ended	All	1 year	-	5 years	-
	70 W	1 year	-	5 years	-
CMH <sup>®</sup> Elliptical	150 W	9 months	-	5 years	-
	100 W	6 months	-	5 years	-

<sup>1</sup> Includes GE covRguard<sup>®</sup> lamps

<sup>2</sup> After date of purchase

<sup>3</sup> Contingent upon maximum rated case temperature: 36 or 60 months as specified on [www.gelighting.com](http://www.gelighting.com)

<sup>4</sup> Linear fluorescent and compact fluorescent operating at 4,000 hours per year, high intensity discharge at 5,000 hours per year.

<sup>5</sup> From date of manufacture

<sup>6</sup> Applies to F55BX lamps rated at 20,000 hours life

Ballast Remedy: GE will, at its option, either (1) provide a credit to Purchaser equal to the current price GE charges Purchaser for the ballast, or (2) provide a free replacement ballast to Purchaser. GE reserves and has the right to examine failed lamps and/or ballasts to determine the cause of failure and patterns of usage.

# GE Lighting

## System Limited Warranty

(See the GE Lighting System and Ballast Limited Warranty at [www.gelighting.com/warranty](http://www.gelighting.com/warranty) for full details and specific lamp cycle requirements.)

### GE Lamps Operating on GE Ballasts

		Lamp Warranty <sup>2</sup>		Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty <sup>5</sup>
Compact Fluorescent Lamp <sup>4</sup>		When Operated on GE Programmed Rapid-Start Ballasts	When Operated on GE Instant-Start Ballasts		
Double Biax <sup>®</sup> : 13-, 18-, 26-watt "DBX" (4-pin base types only)		2 years	-	5 years	-
Triple Biax <sup>®</sup> : 13-, 18-, 26-, 32-, 42-watt "TBX"		2 years	-	5 years	-
High-Output Biax <sup>®</sup> : 57-watt and 70-watt "QBX"		2 years	-	5 years	-
High Lumen Biax <sup>®</sup> 27 W and 39 W		1 year	-	5 years	-
High Lumen Biax <sup>®</sup> 55 W <sup>6</sup>		2 years	-	5 years	-
High Lumen Biax <sup>®</sup> Watt-Miser <sup>®</sup> 25 W (F40/25BX)		3 years	2.5 years	5 years	-
High Lumen Biax <sup>®</sup> 40 W (F40/30BX)		2 years	1 year	5 years	-
Linear Fluorescent Lamp <sup>1,4</sup>		When Operated on GE Programmed Rapid-Start Ballasts	When Operated on GE Instant-Start Ballasts	Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty <sup>5</sup>
F17T8/XL, F25T8/XL, F32T8 (SP, SPP & SPX)		3 years	2.5 years	5 years	2 years
F17T8/XL/WM, F25T8/XL/WM		3 years	3 years	5 years	2 years
F28T8/XL/SPP, F32T8/25W/SPP, F32T8/XL (SP & SPX)		4 years	3 years	5 years	2 years
F32T8/XL/HL		4 years	4 years	5 years	2 years
F28T8/XL/SPX, F32T8/SXL, F32T8/25W/SPX		5 years	4 years	5 years	2 years
F28T8/SXL, F32T8/25W/SXL		7 years	5 years	5 years	2 years
F96T8, F96T8/HO		-	2 years	5 years	-
F96T8/XL (SP, SPP & SPX), F96T8/XL/WM, F96T8/XL/WMP, F96T8/54W/SPP, F96T8/49W (SPP & SPX)		-	3 years	5 years	-
F28W/TS/HL		3 years	-	5 years	-
F14T5/WM, F21T5/WM, F28T5/WM, F35T5/WM		3.5 years	-	5 years	-
F14T5HE, F21T5HE, F28T5HE, F35T5HE, F54T5/47W, F24T5HO, F39T5HO, F54T5HO, F80T5HO, F54T5/WM		4 years	-	5 years	-
F54T5/XL		5 years	-	5 years	-
HID High Watt Lamps <sup>4</sup>		When Operated on GE Ballasts		Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty <sup>5</sup>
CMH <sup>®</sup> ConstantColor <sup>®</sup> SPXX: 250-, 320-, 350-, 400-watt		1 year	-	5 years	2 years
PulseArc <sup>®</sup> : 250-, 320-, 350-, 400-watt		1 year	-	5 years	2 years
HID Low Watt Lamps <sup>4</sup>		When Operated on GE Ballasts		Electronic Ballast Warranty <sup>3,5</sup>	Electromagnetic Ballast Warranty
CMH <sup>®</sup> PAR	Wattage/Type				
CMH <sup>®</sup> PAR	PAR20, PAR30L, PAR38, PAR64	6 months	-	5 years	-
CMH <sup>®</sup> MR16	All	6 months	-	5 years	-
CMH <sup>®</sup> GU6.5	All	6 months	-	5 years	-
CMH <sup>®</sup> G8.5	20 W	6 months	-	5 years	-
	39 W, 70 W	1 year	-	5 years	-
CMH <sup>®</sup> G12	20 W, 150 W	6 months	-	5 years	-
	39 W, 70 W	1 year	-	5 years	-
CMH <sup>®</sup> Double-ended	All	1 year	-	5 years	-
	70 W	1 year	-	5 years	-
CMH <sup>®</sup> Elliptical	150 W	9 months	-	5 years	-
	100 W	6 months	-	5 years	-

<sup>1</sup> Includes GE covRguard<sup>®</sup> lamps

<sup>2</sup> After date of purchase

<sup>3</sup> Contingent upon maximum rated case temperature; 36 or 60 months as specified on [www.gelighting.com](http://www.gelighting.com)

<sup>4</sup> Linear fluorescent and compact fluorescent operating at 4,000 hours per year, high intensity discharge at 5,000 hours per year.

<sup>5</sup> From date of manufacture

<sup>6</sup> Applies to F55BX lamps rated at 20,000 hours life

Ballast Remedy: GE will, at its option, either (1) provide a credit to Purchaser equal to the current price GE charges Purchaser for the ballast, or (2) provide a free replacement ballast to Purchaser. GE reserves and has the right to examine failed lamps and/or ballasts to determine the cause of failure and patterns of usage.