

Pass & Seymour



On-Q/Legrand® Home Systems Enclosures

Part Number	Description	Rail Space (Inches)	Enclosure Color	Door Color	Cover / Door	Door Swing (Left or Right)	UL Listed (Fire and Burglary)	UL Listed (Communication Circuit Equipment)	Lock
1267077-01	12" Value Line Modular Enclosure 13"H x 14.25"W x 4"D	24	Gray	White	Screw on	N/A	N/A	•	N/A
364257-01	24" Value Line Modular Enclosure 25"H x 14.25"W x 4"D	48	Gray	White	Screw on	N/A	N/A	•	N/A
363474-01	14" Premium Line Modular Enclosure 14"H x 14.25"W x 4"D	24	White	White	Hinged	R	•	•	•
363475-01	28" Premium Line Modular Enclosure 28"H x 14.25"W x 4"D	52	White	White	Hinged	R	•	•	•
363476-01	42" Premium Line Modular Enclosure 42"H x 14.25"W x 4"D	80	White	White	Hinged	R	•	•	•
364451-01	28" PLUS™ Series Enclosure 28"H x 14.25"W x 6.5"D	68	White	White	Hinged	R	•	•	•
364451-02	42" PLUS™ Series Enclosure 42"H x 14.25"W x 6.5"D	96	White	White	Hinged	R	•	•	•
364591-01	28" Custom Enclosure 28"H x 14.25"W x 4"D	52	White	Opt.	Hinged Opt. Door	L ¹ or R	•	•	Incl. on Opt. Door
364592-01	42" Custom Enclosure 42"H x 14.25"W x 4"D	80	White	Opt.	Hinged Opt. Door	L ¹ or R	•	•	Incl. on Opt. Door
F7810	20" FoxBox™ 19.25"H x 14.25"W x 3.625"D	N/A	White	White	Screw on	N/A	•	•	N/A
F7811	20" FoxBox™ 19.25"H x 14.25"W x 3.625"D	N/A	White	White	Hinged	R	•	•	Opt. Door
F7814	42" FoxBox™ 42"H x 14.25"W x 3.625"D	N/A	White	White	Screw on	N/A	•	•	N/A
F7815	42" FoxBox™ 42"H x 14.25"W x 3.625"D	N/A	White	White	Hinged	R	•	•	Opt. Door
F7498	32" Titan™ 32"H x 14.25"W x 3.625"D	N/A	White	Gray/Blue on Door	Hinged Opt. Door	L or R	•	•	Incl. on Opt. Door
F7499	42" Titan™ 42"H x 14.25"W x 3.625"D	N/A	White	Gray/Blue on Door	Hinged Opt. Door	L or R	•	•	Incl. on Opt. Door

¹PLUS Series Door facilitates right hand swing only

• = Included With Enclosure

L = Left, R = Right

Opt. = Optional

N/A = Not Available