



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FD2125 Type FD BRKR 2P 125A/ 250VDC Max 10K/600VAC Max 18 *Eaton Corp*

Catalog Number	FD2125
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 125 A, 600 Vac, 250 VDC, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac
Weight per unit	3.0 (lbs/each)
Product Category	2 Pole

Features

Current Rating	125 A
dimensions	3.3800 IN X 5.1000 IN X 6.0000 IN
media	Yes
Poles	2
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE FD BRKR 2P 125A/ 250VDC MAX 10K/600VAC MAX 18
extra long description	ETN FD2125 FD CB 2P 125A/ 250VDC MA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 125 A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac
Product Type	FD CB 2P 125A/ 250VDC Max 10K/600VAC Max

Manufacturer Information

Brand	Eaton
GTIN	00786679312315
Manufacturers Part Number	FD2125
UPC	786679312315

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3

Uses, Certifications, and Standards

Application	Other
standard	UL Listed