




GE  
Lighting

**28106 - F96T8/SP35/ECO**

GE Ecolux® T8

- Passes TCLP, which can lower disposal costs.



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Single Pin (Fa8)
Rated Life	15000.0 hrs
Rated Life (instant start) @ Time	15000 h @ 3 h 20000 h @ 12 h
Bulb Material	Soda lime
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	123 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	5700.0
Mean Lumens	5130.0
Nominal Initial Lumens per Watt	96
Color Temperature	3500.0 K
Color Rendering Index (CRI)	75.0

**ELECTRICAL CHARACTERISTICS**

Wattage	59.0
---------	------

**DIMENSIONS**

Maximum Overall Length (MOL)	96.0000 in(2438.4 mm)
Nominal Length	96.000 in(2438.4 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	28106
Description	F96T8/SP35/ECO
Standard Package	Case
Standard Package GTIN	10043168281062
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168281065




GE  
Lighting

**28106 - F96T8/SP35/ECO**

GE Ecolux® T8

- Passes TCLP, which can lower disposal costs.



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Single Pin (Fa8)
Rated Life	15000.0 hrs
Rated Life (instant start) @ Time	15000 h @ 3 h
	20000 h @ 12 h
Bulb Material	Soda lime
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	123 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	5700.0
Mean Lumens	5130.0
Nominal Initial Lumens per Watt	96
Color Temperature	3500.0 K
Color Rendering Index (CRI)	75.0

**ELECTRICAL CHARACTERISTICS**

Wattage	59.0
---------	------

**DIMENSIONS**

Maximum Overall Length (MOL)	96.0000 in(2438.4 mm)
Nominal Length	96.000 in(2438.4 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	28106
Description	F96T8/SP35/ECO
Standard Package	Case
Standard Package GTIN	10043168281062
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168281065