



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## FC52GL Ehu Strain Relief .52 - .73

*Pass & Seymour/Legrand*

Catalog Number	FC52GL
Manufacturer	Pass & Seymour/Legrand
Description	FC52GL: Extra-Hard Use, Closed Mesh, Cable Diameter 0.52 - 0.73 Inches, Mesh Length 6.5-In
Weight per unit	0.4310 (lbs/each)
Product Category	Cable & Cord Grips

### Features

Cable Size	Cable Dia. Range: 0.520-0.730; Mesh Length: 9.00
Cable Type	Various Types of Electrical Conductor/Cable
load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.

### Descriptions

Construction	Various Types of Pulling, Support and Strain Relief Grips
Description	EHU STRAIN RELIEF .52 - .73
extra long description	P&S FC52GL EHU STRAIN RELIEF .52 -
Long Description	FC52GL: Extra-Hard Use, Closed Mesh, Cable Diameter 0.52 - 0.73 inches, Mesh Length 6.5-in
Product Type	Ehu Strain Relief .52 - .73
Special Features	Wire mesh grips for Turnlok® and EHU straight blade plugs and connectors provide additional strain-relief for wiring device plugs and connectors used on portable equipment in commercial and institutional applications, and industrial plant and construction site areas, which incur abnormally high abuse.

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007998795
Manufacturers Part Number	FC52-GL
UPC	785007998795

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Flexcor® Turnlok®/EHU Strain Relief Grip

### Packaging

Carton	1
Package	20
Weight Per each	0.431



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Industrial
Capacity	Various Cable Diameter Ranges
Mounting	Consult the Factory for Mounting Recommendations
standard	UL/CSA Approval (consult factory)