

**NEW!**  
more on  
reverse

# Floor Box for New Concrete

## Non-Metallic Box with SIX Conduit Hubs • Reversible Leveling Ring

### SIDE A

Fits 6" round covers with a 3-1/2" screw hole pattern




### SIDE B

Fits 6" round covers with a 3-3/8" screw hole pattern

**NEW!**  
**REVERSIBLE**  
**Leveling Ring**



**THREE options**  
for low voltage  
divider positioning



Arlington's FLOOR BOXES, COVER KITS, and accessories **FOR NEW CONCRETE** are the low cost, *convenient* way to install a receptacle *flush with a new floor*.

Made of heavy-duty plastic, our **NEW FLBC4502 4.5" non-metallic concrete floor box** has more! – SIX conduit hubs and FOUR plugs. And THREE options for positioning the low voltage divider in the box.

The **NEW FLBC4502LR leveling ring** makes installing a cover easy on ANY 4.5" concrete box including our FLBC4500 and the new FLBC4502. **It's REVERSIBLE!** Side A fits any 6" round cover with a 3-1/2" screw hole pattern. Side B has a second set of holes that fits 6" covers with a 3-3/8" screw hole pattern.



Arlington offers a variety of **cover kits** to fit our concrete boxes – Round with flip lids or threaded plugs in brass or nickel-plated brass. Metal trapdoor covers with three device options. *And in plastic, in six colors.*

Get a great-looking, time-saving receptacle installation *in new concrete* with floor box kits, covers and more - from Arlington!


### ARLINGTON COVER KITS for FLBC4502 and FLBC4500



1 Stauffer Industrial Park  
Scranton, PA 18517  
**800/233.4717**  
**Fax 570/562.0646**  
[www.aifittings.com](http://www.aifittings.com)

# Concrete Floor Boxes, Cover Kits, Accessories


*Put a Receptacle in New Concrete – The Easy, Low Cost Way!*




CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	CONCRETE FLOOR BOXES & LEVELING RINGS DESCRIPTION	UNIT PKG	STD PKG
FLBC4502	34004	4.5" Non-metallic <b>ROUND BOX WITH (6) CONDUIT HUBS</b> for New Concrete Pours. UL Listed. Includes divider, pour cap, (4) 3/4" plugs and (2) 1" plugs for unused hubs.	1	5
FLBC4502LR	34005	<b>REVERSIBLE LEVELING RING</b> for Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers	1	10
FLBC4500	22010	4.5" Non-metallic <b>ROUND BOX WITH (4) CONDUIT HUBS</b> for New Concrete Pours. UL Listed. Includes divider, pour cap, (2) 3/4" plugs and (1) 1" plug for unused hubs.	1	5
FLBC4500LR	22011	<b>LEVELING RING</b> for Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers	1	10
FLBC4500LRBE	20745	<b>LEVELING RING/BOX EXTENDER</b> Extends installed boxes up to 2". For Arlington FLBC4502, FLBC4500 and others' 4.5" boxes and 6" covers.	1	10

### EASY TO INSTALL CONCRETE BOXES

- 1 Set concrete floor box into position. Secure in place through molded mounting ears. Option: Use 1/4-20 screws to level/position the box.
- 2 Install conduit as needed using PVC cement. Pull wires through conduit as required.
- 3 Install plugs (provided) w/ PVC cement to seal unused openings.
- 4 Install pour cap. Pour concrete to finished depth.
- 5 After concrete has cured, remove pour cap. Use a saw to cut box to finished floor height.



**Complete the installation with a leveling ring and one of these cover trim kits.**



CATALOG NUMBER	UPC/DCI/NAED MFG. #018997	DESCRIPTION FINISH/COLOR, COVER STYLE	NOTES	UNIT PKG	STD PKG
<b>METAL COVER KITS</b> with Leveling Ring included					
FLB6230MBLR	34008	COVER KIT 6" Round, Brass w (2) flip lids	* hole pattern fits leveling ring	1	10
FLB6230NLLR	34009	COVER KIT 6" Round, Nickel-plated w (2) flip lids	* hole pattern fits leveling ring	1	10
FLB6220MBLR	22959	COVER KIT 6" Round, Brass w (2) threaded plugs	* hole pattern fits leveling ring	1	10
FLB6220NLLR	22960	COVER KIT 6" Round, Nickel-plated w (2) threaded plugs	* hole pattern fits leveling ring	1	10

*Metal Cover Kits also available without the Leveling Ring. Delete suffix 'LR'.*

### PLASTIC COVER KITS

FLBC4520GY	09674	COVER KIT 6" Round, Light Almond – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520W	13838	COVER KIT 6" Round, White – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520GY	09673	COVER KIT 6" Round, Gray – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520BR	09672	COVER KIT 6" Round, Brown – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520CA	09669	COVER KIT 6" Round, Caramel – Plastic gasketed cover, mounting plate, leveling ring		1	10
FLBC4520BL	09671	COVER KIT 6" Round, Black– Plastic gasketed cover, mounting plate, leveling ring		1	10

### TRAPDOOR STYLE, METAL COVERS

Pre-mounted gasket, installed decorator-style UL LISTED receptacle

FLBT6620UMB	22047	Trapdoor Cover Round, Brass. Tamper-resistant 20A receptacle with (2) USB ports		1	10
FLBT6620MB	22052	Trapdoor Cover Round, Brass. Tamper-resistant 20A receptacle		1	10
FLBT6620GMB	22053	Trapdoor Cover Round, Brass. Tamper-resistant GFCI 20A receptacle		1	10
FLBT6620UNL	22048	Trapdoor Cover Round, Nickel-plated. Tamper-resistant 20A receptacle with (2) USB ports		1	10
FLBT6620NL	22054	Trapdoor Cover Round, Nickel-plated. Tamper-resistant 20A receptacle		1	10
FLBT6620GNL	22055	Trapdoor Cover Round, Nickel-plated. Tamper-resistant GFCI 20A receptacle		1	10

*Trapdoor cover kits also available with 15A receptacles. See FLBT6615 series on our website.*



Distributed by

# Arlington

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com