



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FLL1504KUK 150W Led FLD 40K KNCK MNT 14665LM

Hubbell Lighting/Current Hli

Catalog Number	FLL1504KUK
Manufacturer	Hubbell Lighting/Current Hli
Description	FLL Led Large Flood, Mounting Type: Knuckled Slipfitter (2 3/8 In Od Tennon), Light Distribution: Nema 6X6 (HXV), Wattage: 150 W, Color Temperature: 4000 K, 80 Cri, Light Output: 14665 LM, Voltage Rating: 120-277 Vac, Color: Dark Bronze.
Weight per unit	20.0 (lbs/each)
Product Category	Led Floodlights

Features

Fixture Type	Floodlighting
Lamp Type	LED
lumens	14665
Voltage Rating	120-277 VAC

Material, Color, and Finish

Color	Dark Bronze
-------	-------------

Descriptions

Description	150W LED FLD 40K KNCK MNT 14665LM
extra long description	HUB-LT FLL-150-4K-U-K FLL LED Flood
Long Description	FLL LED Large Flood, Mounting Type: Knuckled Slipfitter (2 3/8 in OD tennon), Light Distribution: NEMA 6x6 (HxV), Wattage: 150 W, Color Temperature: 4000 K, 80 CRI, Light Output: 14665 lm, Voltage Rating: 120-277 VAC, Color: Dark Bronze.
Product Type	FLL Led Floodlight, Mount Type: Knuckle

Manufacturer Information

Brand	Hubbell Lighting, Inc.
GTIN	00785988033690
Manufacturers Part Number	FLL-150-4K-U-K
UPC	785988033690

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Floodlighting

Packaging

Carton	1
Weight Per each	20



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

Knuckled Slipfitter (2 3/8" OD tennon)

CSA;Damp Listed;IP Rated;UL;UL1598A;Wet Listed