

# Eaton FL3K40

Catalog Number: FL3K40

Eaton Cooper Power series Edison fuse link, 40A, Fast-acting, EEI-NEMA, Removable buttonhead

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Cooper Power series Edison fuse link	FL3K40
	<b>UPC</b>
	051712145923
<b>Product Length/Depth</b>	<b>Product Height</b>
0.75 in	23 in
<b>Product Width</b>	<b>Product Weight</b>
0.75 in	0.1 lb
<b>Warranty</b>	<b>Certifications</b>
Not Applicable	IEEE Certified
	IEC Rated

## Additional Specifications

### Quantity

25

### Type

Fast-acting, EEI-NEMA

## Descriptions

### Application

Medium voltage fused cutouts

## Electrical Ratings

### Amperage Rating

40 A

## Resources

### Catalogs

[Edison tin and silver fuse links](#)

### Specifications and datasheets

[Eaton Specification Sheet - FL3K40](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton FL3K40

Catalog Number: FL3K40

Eaton Cooper Power series Edison fuse link, 40A, Fast-acting, EEI-NEMA, Removable buttonhead

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Cooper Power series Edison fuse link	FL3K40
	<b>UPC</b>
	051712145923
<b>Product Length/Depth</b>	<b>Product Height</b>
0.75 in	23 in
<b>Product Width</b>	<b>Product Weight</b>
0.75 in	0.1 lb
<b>Warranty</b>	<b>Certifications</b>
Not Applicable	IEEE Certified
	IEC Rated

## Additional Specifications

### Quantity

25

### Type

Fast-acting, EEI-NEMA

## Descriptions

### Application

Medium voltage fused cutouts

## Electrical Ratings

### Amperage Rating

40 A

## Resources

### Catalogs

[Edison tin and silver fuse links](#)

### Specifications and datasheets

[Eaton Specification Sheet - FL3K40](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)