



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **FP30115100BLACK Thin-Wall Heat Shrink Tubing, 1/2 - 100', BK** *Minnesota Mining (3M)*

Catalog Number	FP30115100BLACK
Manufacturer	Minnesota Mining (3M)
Description	3M™ Heat Shrink Tubing FP-301 Is A General Purpose, Thin Wall Tubing That Provides A Balance Of Electrical, Physical and Chemical Properties, Making It Ideal For Industrial and Military Applications. This Tubing Has A 2:1 Shrink Ratio and Provides Flame Retardant Insulation For 600V Rated Applications. It Has A Flexible Polyolefin Construction That Offers Moisture Seal Protection.
Weight per unit	0.0370 (lbs/each)
Product Category	Insulating Materials

### **Features**

continuous operating temperat	-67 degrees to 275 degrees
Dielectric Strength	900
flammability	Pass
Inside Diameter	0.75
outside diameter	1.5
Shrink Ratio	2:1

### **Material, Color, and Finish**

Color	Black
-------	-------

### **Dimensions and Weight**

Length	1200
Thickness	0.04



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	THIN-WALL HEAT SHRINK TUBING, 1/2 - 100', BK
extra long description	3M FP1.500BK100'L FP301 1 1/2" BK X
Features	3M™ Heat Shrink Tubing FP-301 is color coded for quick and easy identification of the wire. This split resistant, flame retardant tubing is used as shrink fit, electrical insulation over cable splices or terminations. The high expansion ratio tubing is mechanically tough, easily markable and resists cold flow. It is ideal for lightweight wire harness covering, fire resistant covering, wire marking, wire bundling and component packaging. It withstands temperatures of 67 to 275 degrees F ( 55 to 135 degrees
Long Description	3M™ Heat Shrink Tubing FP-301 is a general purpose, thin wall tubing that provides a balance of electrical, physical and chemical properties, making it ideal for industrial and military applications. This tubing has a 2:1 shrink ratio and provides flame retardant insulation for 600V rated applications. It has a flexible polyolefin construction that offers moisture seal protection.
Product Type	FP301 1 1/2" BK X 100FT, 100FT/SPL
Special Features	Flexible, Polyolefin

## Manufacturer Information

Brand	3M
GTIN	00054007085140
Manufacturers Part Number	FP1.500BK100'L
UPC	054007085140

## Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Single (Thin) Wall

## Packaging

Carton	200
Weight Per each	0.037

## Uses, Certifications, and Standards

standard	UL, CSA, ABS
----------	--------------