



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FML4W485000LM840 FML4W 48 5000LM 840 ZT Mvolt

Lithonia Lighting - Acuity

Catalog Number	FML4W485000LM840
Manufacturer	Lithonia Lighting - Acuity
Description	The FML4W Wide Housing Led Wrap Is Designed With The Renovator In Mind. While Compatible With New Construction, It'S No Mystery The Flexibility Of The FML4W Will Keep Renovation Simple. A Wider Housing Easily Covers Up Existing Blemishes From Older Fixtures, Which Means Less Maintenance Upon Installation. This Is Capped Off With Standard 0-10V Dimming.
Weight per unit	9.0 (lbs/each)
Product Category	Lighting

Features

average life	60
dimensions	48 x 10 x 3
Lamp Included	Yes
Lamp Type	LED - Static
lumens	5000
Material	Steel
Power Source	Hardwired
Voltage Rating	120-277
Warranty	5
Wattage	53

Material, Color, and Finish

Finish	Semi-Gloss
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	3
Length	48
Width	10



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	FML4W 48 5000LM 840 ZT MVOLT
extra long description	LITH FML4W 48 5000LM 840 ZT MVOLT W
Features	Contractor Select
Long Description	The FML4W wide housing LED wrap is designed with the renovator in mind. While compatible with new construction, it's no mystery the flexibility of the FML4W will keep renovation simple. A wider housing easily covers up existing blemishes from older fixtures, which means less maintenance upon installation. This is capped off with standard 0-10V dimming.
Product Type	Wraparound

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994026815
Manufacturers Part Number	FML4W 48 5000LM 840 ZT MVOLT
UPC	194994026815

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Wraparound

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight Per each	9

Uses, Certifications, and Standards

Application	Government,Hospitality,Offices & Banks,Residential,Utility, Closet
environmental conditions	Indoor
standard	CSADLC Standard,ENERGY STAR