



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FMLWLLNK48AL048S 4' Led Wrap Lumen & Kelvin Select 2, 000-4, 000LM

Lithonia Lighting - Acuity

| | |
|------------------|---|
| Catalog Number | FMLWLLNK48AL048S |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | FMLWL LNK Provides 3CCT Switchable White Technology and Adjustable Lumen Output (Alo) For Customization Of Your Space. With 3CCT Capability You Simply Adjust The Color Temperature From Warm White (3000K) to Daylight (5000K). With Alo Technology, Dial to Desired Light Output (Dim-High) to Match The Needs Of Any Job Site. The FMLWL Led Wraparound Provides Ambient Lighting For Surface-Mount Applications. The FMLWL Wrap Is Ideal For Both Residential and Commercial Use, Ideally In Kitchens, Laundry Rooms, Utili |
| Weight per unit | 6.5 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-------------------------------|--|
| average life | 50,000 |
| dimensions | 47.4 x 5.5 x 2.6 |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 2000 LM,2900 LM,3000 LM,4000 LM,Switchable |
| Material | Steel |
| Maximum Operating Temperature | 40 |
| Power Source | Hardwired |
| Shape | Rectangular |
| Voltage Rating | 120 |
| Warranty | 5 |
| Wattage | 42 |

Material, Color, and Finish

| | |
|-----------------------------|------------------|
| Color | White |
| color rendering index (cri) | 85 |
| color temperature | 3000 ,4000 ,5000 |
| Finish | Gloss |
| Style | CONTEMPORARY |

Dimensions and Weight

| | |
|--------|------|
| Height | 2.6 |
| Length | 47.4 |
| Width | 5.5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 4' LED WRAP LUMEN & KELVIN SELECT 2,000-4,000LM |
| extra long description | LITH FMLWL LNK 48 ALO4 8SWW2 Wrapar |
| Features | Contractor Select |
| Long Description | FMLWL LNK provides 3CCT Switchable White Technology and Adjustable Lumen Output (ALO) for customization of your space. With 3CCT capability you simply adjust the color temperature from warm white (3000K) to daylight (5000K). With ALO technology, dial to desired light output (dim-high) to match the needs of any job site. The FMLWL LED Wraparound provides ambient lighting for surface-mount applications. The FMLWL wrap is ideal for both residential and commercial use, ideally in kitchens, laundry rooms, utili |
| Product Type | Wraparound |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Lithonia Lighting |
| GTIN | 00194995061037 |
| Manufacturers Part Number | FMLWL LNK 48 ALO4 8SWW2 |
| UPC | 194995061037 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | Wraparound |

Trade Size

| | |
|---------------|-----|
| aperture size | 4FT |
|---------------|-----|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight | 5 |
| Weight Per each | 6.5 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Government,Hospitality,Offices & Banks,Residential,Utility, Closet |
| environmental conditions | Indoor |
| Mounting | SURFACE |
| standard | cUL,ULENERGY STAR |