ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



FSC405R SCONCE BOX

ARLINGTON INDUSTRIES

Catalog Number	FSC405R
Manufacturer	ARLINGTON INDUSTRIES
Description	Low Profile sconce box. Installs with a 4" hole saw on 1/2" or 5/8" drywall. 5 cu. in.
Weight per unit	0.1000 (lbs/each)
Product Category	Lighting Accessories

Features

Material	Plastic
Media	Yes

Material, Color, and Finish

Color	Black

Dimensions and Weight

Size	L(3.500) x W(3.760) x H(0.562)

Descriptions

Description	SCONCE BOX
Long Description	Low Profile sconce box. Installs with a 4" hole saw on 1/2" or 5/8" drywall. 5 cu. in.
Product Type	Shallow Sconce Box
Extra Long Description	ARL FSC405R SHALLOW SCONCE BOX

Manufacturer Information

Brand	Arlington Industries
	ARLINGTON
GTIN	00018997040947
Manufacturers Part Number	FSC405R
UPC	801230

Taxonomies, Classifications, and Categories

Category Description	PLASTIC BOXES

Packaging

Carton	1
Package	10
Weight Per Each	0.1000 (lbs/each)

Uses, Certifications, and Standards

Standard	cULus

Low Profile Sconce Box

Made in USA

NEW!

Perfect for shallow wall cavities or obstructions behind the wall



Never mind obstructions behind the wall.


Install the fixture where YOU want it, with Arlington's low profile sconce box.

FSC405R
Low profile
Sconce Box

Arlington's **Low Profile Sconce Box** offers the time-saving solution to retrofit installations that have shallow wall cavities - or obstructions running behind the wallboard.

This 4" diameter non-metallic box installs in an existing 1/2" *or 5/8*" wall with a 4" hole saw.

- Includes NM cable connector and mounting wings for 1/2" *or 5/8*" drywall and installation screws for the mounting wings



Set for 1/2" wall

Easy-to-install mounting wings


5/8" mounting wing installed

- 4" diameter box accommodates most sconce light canopies, completely hiding the box
- CULUS Listed

Easy installation in **Existing Walls**...



Determine sconce light location. Cut opening with 4" hole saw.




Pipe obstruction behind wall prevents the installation of a typical sconce box. Install mounting wing for 1/2 or 5/8" drywall. Pull cable...



...Inserting it into installed NM94 connector. Tilt box to insert it into the stud cavitiy.



Pull box towards you, into the 4" opening. Flip the retaining wings outward. Tighten screws to secure box to wallboard.



Finished box installation. Ready to install sconce light.

Catalog Number	UPC/DEI/NAED Mfg. #018997	Description SCONCE BOX	Unit/Std Pkg
FSC405R	04094	Non-metallic, 5.0 cubic inch, 4" Dia. Low profile sconce box	1/10

Includes box, NM cable connector, (2) mounting wings for 1/2" drywall, (2) mounting wings for 5/8" drywall and (2) installation screws for 'wings'

Patent pending

Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

©2014 25M Arlington Industries, Inc.