



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FSL25 25W Led Flood 50K 2664LM 120-277V *Hubbell Lighting/Current Hli*

Catalog Number	FSL25
Manufacturer	Hubbell Lighting/Current Hli
Description	N/A, Mounting Type: Knuckle (1/2 In X 14 NPS), Light Distribution: Nema 6X6 (HXV), Wattage: 25 W, 70 Cri, Light Output: 2664 LM, Voltage Rating: 120-277 Vac, Color: Dark Bronze.
Weight per unit	8.4 (lbs/each)
Product Category	Led Floodlights

Features

Fixture Type	Floodlighting
Lamp Type	LED
lumens	2664
Voltage Rating	120-277 VAC

Material, Color, and Finish

Color	Dark Bronze
-------	-------------

Dimensions and Weight

Size	4.03 in x 7.49 in x 8.02 in
------	-----------------------------

Descriptions

Description	25W LED FLOOD 50K 2664LM 120-277V
extra long description	HUB-LT FSL-25 FSL LED Decor flood 2
Long Description	N/A, Mounting Type: Knuckle (1/2 in x 14 NPS), Light Distribution: NEMA 6x6 (HxV), Wattage: 25 W, 70 CRI, Light Output: 2664 lm, Voltage Rating: 120-277 VAC, Color: Dark Bronze.
Product Type	FSL Led Decor Flood 25 W 120-277V

Manufacturer Information

Brand	Beacon_Products
GTIN	00785988033485
Manufacturers Part Number	FSL-25
UPC	785988033485

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Floodlighting

Packaging

Carton	1
Weight Per each	8.3999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Automotive

Dealers;Educational;Healthcare;Hospitality;Manufacturing;Offices;Retail;V

Mounting

Knuckle (1/2 in x 14 NPS)

standard

CSA;IP Rated;UL1598A;Wet Listed