



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FTSP45240FMLT Fish Tape, 4.5MM, FTSP45-240FMLT, 240' Tri *Southwire Company*

Catalog Number	FTSP45240FMLT
Manufacturer	Southwire Company
Description	Fish Tape, 240 Foot Tape Length; Extruded Polymer Tape Material; 4.5 Millimeter Diameter Tape Size; Simpull[TM] Brand; End Type Flexible Metal Tube (One End), Non-Conductive Leader (Other End)
Weight per unit	N/A
Product Category	Markers & Marking Tapes - Tape

Features

Tape Length	240 Foot
Tape Size	4.5 Millimeter Diameter

Material, Color, and Finish

Tape Material	Extruded Polymer
---------------	------------------

Descriptions

Additional Information	End Type Flexible Metal Tube (One End), Non-Conductive Leader (Other End); Overall Dimension 22.75 Inch Width x 2 Inch Depth x 22.75 Inch Height; Packaging Type Tube
Commodity Description	TAPE
Description	FISH TAPE, 4.5MM,FTSP45-240FMLT,240' TRI
extra long description	240 FOOT TAPE LENGTH; 580 POUND (FML), 380 POUND (NCT) TENSILE STRENGTH; EXTRUDED POLYMER TAPE MATERIAL; 4.5 MILLIMETER DIAMETER TAPE SIZE; SIMPULL[TM] BRAND; END TYPE FLEXIBLE METAL TUBE (ONE END), NON-CONDUCTIVE LEADER (OTHER END); OVERALL DIMENSION 22.75 INCH WIDTH X 2 INCH DEPTH X 22.75 INCH HEIGHT; PACKAGING TYPE TUBE
Long Description	FISH TAPE, 240 FOOT TAPE LENGTH; EXTRUDED POLYMER TAPE MATERIAL; 4.5 MILLIMETER DIAMETER TAPE SIZE; SIMPULL[TM] BRAND; END TYPE FLEXIBLE METAL TUBE (ONE END), NON-CONDUCTIVE LEADER (OTHER END)
Product Type	Fish Tape

Manufacturer Information

Brand	Southwire
Manufacturers Part Number	FTSP45-240FMLT

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
----------------------	------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0