



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GAR1926 4-2/0CU 2-1/2ips *Burndy LLC*

Catalog Number	GAR1926
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 Awg (Sol)-2/0 Awg (STR), 2-1/2" Pipe, 2-1/2"-2-7/8"Rod, Bright Dipped.
Weight per unit	1.6 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
----------	--------

Descriptions

Description	4-2/0CU 2-1/2IPS
extra long description	BUR GAR1926 4-2/0CU 2 1/2IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 2-1/2" Pipe, 2-1/2"-2-7/8"Rod, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 2-1/2 - 2-7/8 IN, Tube (ips) Size: 2-1/2 IN, Height: 5 IN, Width: 4-1/4 IN, Installation Torque: 240 IN-LB

Manufacturer Information

Brand	BURNDY
GTIN	00781810235805
Manufacturers Part Number	GAR1926
UPC	781810235805

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR

Packaging

Carton	1
Package	15
Weight Per each	1.56



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod
Or Tube, Direct Burial Cable, Fence Post

standard

UL467