



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GAR6434 500MCM Ground Conn

Burndy LLC

Catalog Number	GAR6434
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 300 Kcmil - 500 Kcmil, 3/8" Pipe, 5/8" - 3/4" Rod, #5-#6 Rebar.
Weight per unit	1.6 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER ALLOY
----------	--------------

Descriptions

Description	500MCM GROUND CONN
extra long description	BUR GAR6434 300-500CU 3/8IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 300 kcmil - 500 kcmil, 3/8" Pipe, 5/8" - 3/4" Rod, #5-#6 Rebar.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Height: 3-1/2 IN, Ground Rod Size: 5/8 - 3/4 IN, Tube (ips) Size: 3/8 IN, Rebar Size: #5 (5/8 IN) - #6 (3/4 IN), Installation Torq

Manufacturer Information

Brand	BURNDY
GTIN	00781810238608
Manufacturers Part Number	GAR6434
UPC	781810238608

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR

Packaging

Carton	1
Weight Per each	1.58



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod
Or Tube, Direct Burial Cable, Fence Post

standard

UL467