



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FXS1512 12' Fiberglass Step/Shelf Ladder Ia *Louisville Ladder*

Catalog Number	FXS1512
Manufacturer	Louisville Ladder
Description	Step Ladder, Double Entry, Cross Step Type; Fiberglass Material; 32.5 Inch Base Width; 12 Foot Height to Top Step; 3 Inch Rung Width; 48 Pound Weight; 300 Pound Load Rating; 12 Step(S); Duty Rating Type Ia; Applicable Standard Csa, Asha, Ansi
Weight per unit	45.9 (lbs/each)
Product Category	Hand Tools - Ladders

### Features

Base Width	32.5 Inch
Height to Top Step	12 Foot
Load Rating	300 Pound
Material	Fiberglass
number of steps	12
Rung Width	3 INCH

### Descriptions

Additional Information	Duty Rating Type IA; Applicable Standard CSA, ASHA, ANSI
Commodity Description	LADDERS
Description	12' FIBERGLASS STEP/SHELF LADDER IA
extra long description	CROSS STEP, 2-IN-1 TYPE; FIBERGLASS MATERIAL; 32-3/8 INCH BASE WIDTH; 48 POUND WEIGHT; 300 POUND LOAD RATING; 12 STEP(S); 60 INCH BASE SPREAD; RUNG SIZE 3 INCH DEPTH; RUNG TYPE STANDARD STEP; DUTY RATING TYPE IA; LADDER SIZE 12 FOOT; MAXIMUM REACH 15 FOOT 1 INCH FOOT (SHELF LADDER), 16 FOOT 1 INCH (STEP LADDER); MAXIMUM STANDING HEIGHT 8 FOOT 6 INCH (SHELF LADDER), 9 FOOT 6 INCH (STEP LADDER); APPLICATION ROOFING, BUILDING MAINTENANCE, CONTRACTING AND INDUSTRIAL CONSTRUCTION; APPLICABLE STANDARD ANSI A14.5
Long Description	STEP LADDER, DOUBLE ENTRY, CROSS STEP TYPE; FIBERGLASS MATERIAL; 32.5 INCH BASE WIDTH; 12 FOOT HEIGHT TO TOP STEP; 3 INCH RUNG WIDTH; 48 POUND WEIGHT; 300 POUND LOAD RATING; 12 STEP(S); DUTY RATING TYPE IA; APPLICABLE STANDARD CSA, ASHA, ANSI
Product Type	Step Ladder



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Louisville Ladder
GTIN	00728865133175
Manufacturers Part Number	FXS1512
Model	FXS1500
UPC	728865133175

## Taxonomies, Classifications, and Categories

Category Description	LADDERS
Type	Double Entry, Cross Step

## Packaging

Carton	1
Weight	48 Pound
Weight Per each	45.9007