



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GFRTW20BLK 20A 125VAC Comm TRWR GFR Black *Hubbell Wiring Devices*

Catalog Number	GFRTW20BLK
Manufacturer	Hubbell Wiring Devices
Description	Power Protection Devices, Receptacle, Self Test, Gfci, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black
Weight per unit	0.2600 (lbs/each)
Product Category	Wiring Devices

### Features

Warranty	11160415
----------	----------

### Material, Color, and Finish

Color	Black
-------	-------

### Descriptions

Description	20A 125VAC COMM TRWR GFR BLACK
extra long description	HWDK GFRTW20BLK 20A 125VAC COMM TRW
Features	AUTOGUARD® Self Test Technology 1st introduced by Hubbell over 10 years ago...self test monitoring now required in 2015 UL 943 GFCI Safety Standard... Hubbell AUTOGUARD® GFCI receptacles continually test and monitor for "people protection capability" automatically. This patented safety feature includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost. GFCI auto-monitoring is conducted continuously within every 30 seconds. Also, clear visual indicators are p
Long Description	Power Protection Devices, Receptacle, Self Test, GFCI, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black
Product Type	20A 125VAC Comm TRWR GFR Black

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778999352
Manufacturers Part Number	GFRTW20BLK
series	Heavy Duty
UPC	883778999352

### Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Tamper-Resistant, Weather Resistant



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Package	1
Weight Per each	0.26

## Uses, Certifications, and Standards

nema rating	5-20R
standard	Meets All NEC® Requirements