



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFRTW83W 20A 125VAC Comm HG TRWR GFR White Hubbell Wiring Devices

Catalog Number	GFRTW83W
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacle, Gfci, Tamper and Weather Resistant, Commercial Hospital Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White
Weight per unit	0.3500 (lbs/each)
Product Category	Wiring Devices

Features

Phase	1
Wattage	2500
Wire Size	#14 - #10

Dimensions and Weight

Size	4.12 in x 1.75 in x 1.48 in
------	-----------------------------

Descriptions

Description	20A 125VAC COMM HG TRWR GFR WHITE
extra long description	HWDK GFRTW83W 20A 125VAC COMM HG TR
Features	AUTOGUARD® Self Test Technology 1st introduced by Hubbell over 15 years ago...self test monitoring now required in UL 943 GFCI Safety Standard... Hubbell AUTOGUARD® GFCI receptacles continually test and monitor for "people protection capability" automatically. This patented safety feature includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost. GFCI auto-monitoring is conducted continuously within every 30 seconds. Also, a clear visual indicator is provided
Long Description	Straight Blade Devices, Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White
Product Type	20A 125VAC Comm HG TRWR GFR White
Special Features	Weather and Tamper Resistant, AUTOGUARD Self test Technology, Closed Loop Active Detection

Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00883778999550
Manufacturers Part Number	GFRTW83W
series	Hospital Grade
UPC	883778999550



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Tamper-Resistant, Weather Resistant

Packaging

Carton	1
Package	10
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Commercial Hospital Grade
nema rating	5-20R
standard	Meets All NEC® Requirements