

# Eaton GFTCB115

Catalog Number: GFTCB115

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Single-pole, 120/240 V, GFTCB, Ground fault circuit interrupter, GFI, 5 mA

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR GFCI circuit breaker	GFTCB115
<b>UPC</b>	<b>Product Length/Depth</b>
786680129766	6 in
<b>Product Height</b>	<b>Product Width</b>
1.25 in	3.5 in
<b>Product Weight</b>	<b>Certifications</b>
0.475 lb	UL 943
	UL 489

## Product specifications

### Type

Ground fault personnel protection circuit breakers

### Amperage Rating

15 A

### Voltage rating

120/240 V

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Protection

5 mA

### Interrupt rating

10 kAIC

### Main circuit breaker

GFTCB

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - GFTCB115](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton GFTCB115

Catalog Number: GFTCB115

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Single-pole, 120/240 V, GFTCB, Ground fault circuit interrupter, GFI, 5 mA

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR GFCI circuit breaker	GFTCB115
<b>UPC</b>	<b>Product Length/Depth</b>
786680129766	6 in
<b>Product Height</b>	<b>Product Width</b>
1.25 in	3.5 in
<b>Product Weight</b>	<b>Certifications</b>
0.475 lb	UL 943
	UL 489

## Product specifications

### Type

Ground fault personnel protection circuit breakers

### Amperage Rating

15 A

### Voltage rating

120/240 V

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Protection

5 mA

### Interrupt rating

10 kAIC

### Main circuit breaker

GFTCB

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - GFTCB115](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)